

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282888

Luminaire Tested: P3AS09R25B2750DE010 E3DL1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282888
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRIS
Catalog Number: P3AS09R25B2750DE010 E3DL1GPH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 296.0 lumens
Efficiency: N/A
Efficacy: 22.6 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282888
CATALOG NUMBER: P3AS09R25B2750DE010 E3DL1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1282888

CATALOG NUMBER: P3AS09R25B2750DE010 E3DL1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	66	66	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	189875
5°	177151
10°	141903
15°	96323
20°	58292
25°	34091
30°	19421
35°	10681
40°	5668
45°	2977
50°	1740
55°	1300
60°	1096
65°	1193
70°	1090
75°	932
80°	758
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2977 cd/sqm



TEST NUMBER: P1282888

CATALOG NUMBER: P3AS09R25B2750DE010 E3DL1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.4	24.1
10°-20°	116.7	39.4
20°-30°	66.7	22.5
30°-40°	26.3	8.9
40°-50°	8.1	2.7
50°-60°	3.2	1.1
60°-70°	2.2	0.7
70°-80°	1.2	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	254.7	86.1
0°-40°	281.0	94.9
0°-60°	292.3	98.7
0°-90°	296.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	296.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	866	
5°	805	71
15°	424	117
25°	141	67
35°	40	26
45°	10	8
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1282888
CATALOG NUMBER: P3AS09R25B2750DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	865.9
1°	864.2
2°	857.1
3°	844.7
4°	827.4
5°	804.8
6°	778.2
7°	748.2
8°	713.4
9°	677.8
10°	637.3
11°	597.4
12°	553.6
13°	510.3
14°	465.9
15°	424.3
17.5°	329.0
20°	249.8
22.5°	187.5
25°	140.9
27.5°	104.4
30°	76.7
32.5°	55.4
35°	39.9
37.5°	28.3
40°	19.8
42.5°	13.6
45°	9.6
47.5°	6.8
50°	5.1
52.5°	4.0
55°	3.4
57.5°	3.1
60°	2.5
62.5°	2.3
65°	2.3
67.5°	2.0
70°	1.7
72.5°	1.4
75°	1.1
77.5°	0.8
80°	0.6
82.5°	0.6
85°	0.3
87.5°	0.3



TEST NUMBER: P1282888
CATALOG NUMBER: P3AS09R25B2750DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)