

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282032

Luminaire Tested: P3AS05R55B2750DE010 E3D1WMH_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282032
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R55B2750DE010 E3D1WMH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 2700K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 512.0 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282032

CATALOG NUMBER: P3AS05R55B2750DE010 E3D1WMH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1282032

CATALOG NUMBER: P3AS05R55B2750DE010 E3D1WMH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95		
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89		
3	104	98	94	90	102	97	93	90	95	91	88	92	89	87	90	88	86	84		
4	100	93	88	84	98	92	87	84	90	86	83	88	84	82	86	83	81	79		
5	95	88	82	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75		
6	91	83	78	74	90	82	77	74	81	76	73	80	76	73	78	75	72	71		
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67		
8	83	75	69	66	82	74	69	65	73	69	65	72	68	65	71	68	65	63		
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60		
10	77	68	62	59	76	67	62	59	67	62	59	66	62	59	65	61	58	57		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	148475
5°	143209
10°	148338
15°	146244
20°	135345
25°	109458
30°	65605
35°	22245
40°	6126
45°	2729
50°	785
55°	153
60°	88
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2729 cd/sqm

TEST NUMBER: P1282032

CATALOG NUMBER: P3AS05R55B2750DE010 E3D1WMH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.0	12.3
10°-20°	179.4	35.0
20°-30°	199.4	38.9
30°-40°	62.1	12.1
40°-50°	7.5	1.5
50°-60°	0.6	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	441.7	86.3
0°-40°	503.8	98.4
0°-60°	511.8	100.0
0°-90°	512.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	512.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	677	
5°	651	63
15°	644	179
25°	452	199
35°	83	62
45°	9	7
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1282032

CATALOG NUMBER: P3AS05R55B2750DE010 E3D1WMH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	677.1
1°	674.6
2°	668.0
3°	659.8
4°	652.4
5°	650.6
6°	652.6
7°	656.7
8°	661.3
9°	665.0
10°	666.2
11°	665.4
12°	662.3
13°	657.5
14°	651.8
15°	644.2
16°	635.5
17°	624.4
18°	611.9
19°	597.0
20°	580.0
21°	560.8
22°	538.0
23°	512.9
24°	484.1
25°	452.4
26°	417.6
27°	380.7
28°	341.2
29°	300.5
30°	259.1
31°	217.5
32°	176.8
32.5°	158.7
33°	140.0
34°	108.3
35°	83.1
36°	63.2
37°	46.9
37.5°	40.1
38°	34.8
39°	26.5
40°	21.4
42.5°	13.6
45°	8.8



TEST NUMBER: P1282032

CATALOG NUMBER: P3AS05R55B2750DE010 E3D1WMH_2700K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	5.3
50°	2.3
52.5°	0.8
55°	0.4
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)