

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282950

Luminaire Tested: P3AS09R25B2750DE010 E3DLP1GPH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282950
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R25B2750DE010 E3DLP1GPH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 80CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 184.0 lumens
Efficiency: N/A
Efficacy: 14.0 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282950

CATALOG NUMBER: P3AS09R25B2750DE010 E3DLP1GPH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1282950

CATALOG NUMBER: P3AS09R25B2750DE010 E3DLP1GPH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97	96	95	93
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92	90	88	86
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87	84	82	80
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82	79	76	75
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78	74	71	70
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74	70	67	66
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70	66	63	62
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67	63	60	58
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64	59	56	55
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61	57	54	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	66793
5°	64098
10°	56133
15°	45131
20°	34676
25°	26227
30°	18965
35°	12582
40°	7643
45°	4435
50°	2831
55°	2294
60°	2017
65°	1764
70°	1475
75°	1440
80°	1137
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4435 cd/sqm

TEST NUMBER: P1282950

CATALOG NUMBER: P3AS09R25B2750DE010 E3DLP1GPH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.5	14.4
10°-20°	55.0	29.9
20°-30°	49.7	27.0
30°-40°	29.9	16.2
40°-50°	11.9	6.4
50°-60°	5.5	3.0
60°-70°	3.3	1.8
70°-80°	1.8	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	131.2	71.3
0°-40°	161.0	87.5
0°-60°	178.4	96.9
0°-90°	184.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	184.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	305	
5°	291	27
15°	199	55
25°	108	50
35°	47	30
45°	14	12
55°	6	5
65°	3	3
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1282950

CATALOG NUMBER: P3AS09R25B2750DE010 E3DLP1GPH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	304.6
1°	304.6
2°	303.2
3°	300.1
4°	296.0
5°	291.2
6°	284.8
7°	277.7
8°	269.4
9°	261.0
10°	252.1
11°	241.8
12°	231.2
13°	220.6
14°	210.0
15°	198.8
17.5°	172.4
20°	148.6
22.5°	127.1
25°	108.4
27.5°	90.9
30°	74.9
32.5°	60.2
35°	47.0
37.5°	35.9
40°	26.7
42.5°	19.5
45°	14.3
47.5°	10.9
50°	8.3
52.5°	6.9
55°	6.0
57.5°	5.2
60°	4.6
62.5°	3.7
65°	3.4
67.5°	2.9
70°	2.3
72.5°	2.0
75°	1.7
77.5°	1.4
80°	0.9
82.5°	0.6
85°	0.6
87.5°	0.3



TEST NUMBER: P1282950

CATALOG NUMBER: P3AS09R25B2750DE010 E3DLP1GPH_4000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)