

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282961

Luminaire Tested: P3AS09R25B2750DE010 E3DLP1LI_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282961
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R25B2750DE010 E3DLP1LI_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 80CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 402.0 lumens
Efficiency: N/A
Efficacy: 30.7 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282961
CATALOG NUMBER: P3AS09R25B2750DE010 E3DLP1LI_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1282961
 CATALOG NUMBER: P3AS09R25B2750DE010 E3DLP1LI_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	65	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58	58	58	58
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	59	56	55	55	55	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145953
5°	140017
10°	122665
15°	98593
20°	75747
25°	57318
30°	41424
35°	27519
40°	16688
45°	9706
50°	6209
55°	5046
60°	4386
65°	3891
70°	3206
75°	3219
80°	2399
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9706 cd/sqm



TEST NUMBER: P1282961
 CATALOG NUMBER: P3AS09R25B2750DE010 E3DLP1LI_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.9	14.4
10°-20°	120.1	29.9
20°-30°	108.6	27.0
30°-40°	65.2	16.2
40°-50°	25.9	6.4
50°-60°	12.0	3.0
60°-70°	7.3	1.8
70°-80°	3.9	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	286.6	71.3
0°-40°	351.9	87.5
0°-60°	389.7	96.9
0°-90°	402.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	402.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	666	
5°	636	58
15°	434	120
25°	237	109
35°	103	65
45°	31	26
55°	13	12
65°	8	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1282961
CATALOG NUMBER: P3AS09R25B2750DE010 E3DLP1LI_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	665.6
1°	665.6
2°	662.4
3°	655.5
4°	646.8
5°	636.1
6°	622.3
7°	606.7
8°	588.5
9°	570.3
10°	550.9
11°	528.3
12°	505.1
13°	481.9
14°	458.8
15°	434.3
17.5°	376.7
20°	324.6
22.5°	277.6
25°	236.9
27.5°	198.7
30°	163.6
32.5°	131.6
35°	102.8
37.5°	78.3
40°	58.3
42.5°	42.6
45°	31.3
47.5°	23.8
50°	18.2
52.5°	15.0
55°	13.2
57.5°	11.3
60°	10.0
62.5°	8.1
65°	7.5
67.5°	6.3
70°	5.0
72.5°	4.4
75°	3.8
77.5°	3.1
80°	1.9
82.5°	1.3
85°	1.3
87.5°	0.6



TEST NUMBER: P1282961
CATALOG NUMBER: P3AS09R25B2750DE010 E3DLP1LI_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)