

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282085

Luminaire Tested: P3AS05R55B2750DE010 E3DLD1MW_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282085
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R55B2750DE010 E3DLD1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 4000K CCT AND, 80CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 337.0 lumens
Efficiency: N/A
Efficacy: 57.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282085

CATALOG NUMBER: P3AS05R55B2750DE010 E3DLD1MW_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1282085

CATALOG NUMBER: P3AS05R55B2750DE010 E3DLD1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93		91
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89	86	84		82
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82	79	76		74
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76	73	69		68
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71	67	64		62
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66	62	58		57
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62	57	54		52
8	73	62	55	51	72	62	55	51	60	54	50		59	54	50		58	53	50		48
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55	50	46		45
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		52	47	43		42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	63372
5°	62558
10°	60097
15°	56209
20°	51268
25°	45753
30°	40006
35°	33247
40°	26192
45°	17769
50°	10848
55°	5620
60°	5219
65°	4981
70°	4616
75°	4067
80°	4041
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17769 cd/sqm

TEST NUMBER: P1282085

CATALOG NUMBER: P3AS05R55B2750DE010 E3DLD1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.7	7.9
10°-20°	69.2	20.5
20°-30°	86.6	25.7
30°-40°	77.4	23.0
40°-50°	45.3	13.4
50°-60°	15.6	4.6
60°-70°	9.5	2.8
70°-80°	5.3	1.6
80°-90°	1.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	182.5	54.2
0°-40°	259.9	77.1
0°-60°	320.8	95.2
0°-90°	337.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	337.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	289	
5°	284	27
15°	248	69
25°	189	87
35°	124	77
45°	57	45
55°	15	16
65°	10	9
75°	5	5
85°	1	2
90°	0	

TEST NUMBER: P1282085

CATALOG NUMBER: P3AS05R55B2750DE010 E3DLD1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	289.0
2.5°	287.4
5°	284.2
7.5°	277.8
10°	269.9
12.5°	259.9
15°	247.6
17.5°	234.4
20°	219.7
22.5°	204.6
25°	189.1
27.5°	173.5
30°	158.0
32.5°	141.3
35°	124.2
37.5°	107.5
40°	91.5
42.5°	74.4
45°	57.3
47.5°	43.8
50°	31.8
52.5°	20.7
55°	14.7
57.5°	13.1
60°	11.9
62.5°	10.7
65°	9.6
67.5°	8.4
70°	7.2
72.5°	6.0
75°	4.8
77.5°	4.0
80°	3.2
82.5°	2.0
85°	1.2
87.5°	0.8
90°	0.0

(END OF REPORT)