

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282091

Luminaire Tested: P3AS05R55B2750DE010 E3DLD1WH\_5000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1282091  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R55B2750DE010 E3DLD1WH\_5000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 5000K CCT AND, 80CRI , E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 360.0 lumens  
Efficiency: N/A  
Efficacy: 61.0 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1282091

CATALOG NUMBER: P3AS05R55B2750DE010 E3DLD1WH\_5000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1282091

CATALOG NUMBER: P3AS05R55B2750DE010 E3DLD1WH\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 102 | 103 | 100 | 98  |  | 99  | 97  | 95  |  | 95  | 94  | 93  | 91  |
| 2   | 105 | 100 | 95  | 91  | 103 | 98  | 93  | 90  | 94  | 91  | 88  |  | 91  | 88  | 86  |  | 89  | 86  | 84  | 82  |
| 3   | 99  | 91  | 85  | 81  | 97  | 90  | 84  | 80  | 87  | 82  | 79  |  | 85  | 81  | 77  |  | 82  | 79  | 76  | 74  |
| 4   | 93  | 84  | 77  | 72  | 91  | 83  | 77  | 72  | 80  | 75  | 71  |  | 78  | 74  | 70  |  | 76  | 73  | 69  | 68  |
| 5   | 87  | 77  | 71  | 66  | 85  | 76  | 70  | 65  | 75  | 69  | 65  |  | 73  | 68  | 64  |  | 71  | 67  | 64  | 62  |
| 6   | 82  | 72  | 65  | 60  | 80  | 71  | 64  | 60  | 69  | 64  | 59  |  | 68  | 63  | 59  |  | 66  | 62  | 58  | 57  |
| 7   | 77  | 67  | 60  | 55  | 76  | 66  | 59  | 55  | 65  | 59  | 54  |  | 63  | 58  | 54  |  | 62  | 57  | 54  | 52  |
| 8   | 73  | 62  | 55  | 51  | 72  | 62  | 55  | 51  | 60  | 54  | 50  |  | 59  | 54  | 50  |  | 58  | 53  | 50  | 48  |
| 9   | 69  | 58  | 51  | 47  | 68  | 58  | 51  | 47  | 57  | 51  | 47  |  | 56  | 50  | 46  |  | 55  | 50  | 46  | 45  |
| 10  | 65  | 55  | 48  | 44  | 64  | 54  | 48  | 44  | 53  | 47  | 43  |  | 52  | 47  | 43  |  | 52  | 47  | 43  | 42  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 67692 |
| 5°  | 66828 |
| 10° | 64194 |
| 15° | 60046 |
| 20° | 54768 |
| 25° | 48874 |
| 30° | 42741 |
| 35° | 35523 |
| 40° | 27995 |
| 45° | 18979 |
| 50° | 11599 |
| 55° | 6002  |
| 60° | 5614  |
| 65° | 5292  |
| 70° | 4937  |
| 75° | 4321  |
| 80° | 4293  |
| 85° | 3271  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 18979 cd/sqm

TEST NUMBER: P1282091

CATALOG NUMBER: P3AS05R55B2750DE010 E3DLD1WH\_5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 28.5   | 7.9       |
| 10°-20°   | 73.9   | 20.5      |
| 20°-30°   | 92.6   | 25.7      |
| 30°-40°   | 82.6   | 23.0      |
| 40°-50°   | 48.4   | 13.4      |
| 50°-60°   | 16.7   | 4.6       |
| 60°-70°   | 10.1   | 2.8       |
| 70°-80°   | 5.6    | 1.6       |
| 80°-90°   | 1.6    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 195.0  | 54.1      |
| 0°-40°    | 277.6  | 77.1      |
| 0°-60°    | 342.7  | 95.2      |
| 0°-90°    | 360.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 360.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 309 |      |
| 5°  | 304 | 28   |
| 15° | 264 | 74   |
| 25° | 202 | 93   |
| 35° | 133 | 83   |
| 45° | 61  | 48   |
| 55° | 16  | 17   |
| 65° | 10  | 10   |
| 75° | 5   | 6    |
| 85° | 1   | 2    |
| 90° | 0   |      |



TEST NUMBER: P1282091

CATALOG NUMBER: P3AS05R55B2750DE010 E3DLD1WH\_5000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 308.7 |
| 2.5°  | 307.0 |
| 5°    | 303.6 |
| 7.5°  | 296.8 |
| 10°   | 288.3 |
| 12.5° | 277.6 |
| 15°   | 264.5 |
| 17.5° | 250.4 |
| 20°   | 234.7 |
| 22.5° | 218.5 |
| 25°   | 202.0 |
| 27.5° | 185.4 |
| 30°   | 168.8 |
| 32.5° | 150.9 |
| 35°   | 132.7 |
| 37.5° | 114.8 |
| 40°   | 97.8  |
| 42.5° | 79.5  |
| 45°   | 61.2  |
| 47.5° | 46.8  |
| 50°   | 34.0  |
| 52.5° | 22.1  |
| 55°   | 15.7  |
| 57.5° | 14.0  |
| 60°   | 12.8  |
| 62.5° | 11.5  |
| 65°   | 10.2  |
| 67.5° | 8.9   |
| 70°   | 7.7   |
| 72.5° | 6.4   |
| 75°   | 5.1   |
| 77.5° | 4.3   |
| 80°   | 3.4   |
| 82.5° | 2.1   |
| 85°   | 1.3   |
| 87.5° | 0.9   |
| 90°   | 0.0   |

(END OF REPORT)