

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282980

Luminaire Tested: P3AS09R25B2750DE010 E3PH1MW_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282980
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R25B2750DE010 E3PH1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 80CRI , E3PH1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 624.0 lumens
Efficiency: N/A
Efficacy: 47.6 lumens/watt
Spacing Criteria (0/90/45): 0.36 / 0.36 / 0.36
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282980

CATALOG NUMBER: P3AS09R25B2750DE010 E3PH1MW_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1282980

CATALOG NUMBER: P3AS09R25B2750DE010 E3PH1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	99	98						
2	113	109	107	105	111	108	105	103	105	103	101	102	100	99	99	98	97	96						
3	110	106	103	100	108	104	102	99	102	100	98	100	98	96	98	96	95	94						
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92						
5	105	100	96	94	103	99	96	93	97	95	93	96	94	92	95	93	91	90						
6	102	97	94	91	101	97	93	91	95	93	91	94	92	90	93	91	89	89						
7	100	95	92	89	99	95	91	89	94	91	89	93	90	88	92	89	88	87						
8	98	93	90	87	98	93	89	87	92	89	87	91	88	87	90	88	86	85						
9	97	91	88	86	96	91	88	85	90	87	85	89	87	85	89	86	85	84						
10	95	89	86	84	94	89	86	84	88	86	84	88	85	83	87	85	83	83						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	954375
5°	815120
10°	513885
15°	239161
20°	49238
25°	10041
30°	2152
35°	455
40°	229
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 0 cd/sqm

TEST NUMBER: P1282980

CATALOG NUMBER: P3AS09R25B2750DE010 E3PH1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	308.6	49.5
10°-20°	286.6	45.9
20°-30°	27.1	4.3
30°-40°	1.6	0.3
40°-50°	0.1	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	622.3	99.7
0°-40°	623.9	100.0
0°-60°	624.0	100.0
0°-90°	624.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	624.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4352	
5°	3703	309
15°	1054	287
25°	42	27
35°	2	2
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1282980

CATALOG NUMBER: P3AS09R25B2750DE010 E3PH1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	4352.3
2.5°	4190.4
5°	3703.1
7.5°	3044.5
10°	2307.9
12.5°	1667.2
15°	1053.5
17.5°	509.4
20°	211.0
22.5°	83.9
25°	41.5
27.5°	19.5
30°	8.5
32.5°	3.4
35°	1.7
37.5°	0.8
40°	0.8
42.5°	0.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)