

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282988

Luminaire Tested: P3AS09R25B2750DE010 E3PHLP1MW_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282988
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R25B2750DE010 E3PHLP1MW_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 333.0 lumens
Efficiency: N/A
Efficacy: 25.4 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.65
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282988
CATALOG NUMBER: P3AS09R25B2750DE010 E3PHLP1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1282988

CATALOG NUMBER: P3AS09R25B2750DE010 E3PHLP1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68	68	68	68
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59	59	59	59
7	79	69	63	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52	52	52	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49	49	49	49
10	69	59	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	111899
5°	105701
10°	89845
15°	71170
20°	54091
25°	40333
30°	29346
35°	20746
40°	14084
45°	9830
50°	8256
55°	7952
60°	8420
65°	8665
70°	8527
75°	9150
80°	10481
85°	10567

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 11256 cd/sqm



TEST NUMBER: P1282988

CATALOG NUMBER: P3AS09R25B2750DE010 E3PHLP1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.3	13.0
10°-20°	86.8	26.1
20°-30°	76.8	23.1
30°-40°	48.9	14.7
40°-50°	25.9	7.8
50°-60°	19.0	5.7
60°-70°	16.2	4.9
70°-80°	11.4	3.4
80°-90°	4.6	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	206.9	62.1
0°-40°	255.9	76.8
0°-60°	300.8	90.3
0°-90°	333.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	333.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	510	
5°	480	43
15°	314	87
25°	167	77
35°	78	49
45°	32	26
55°	21	19
65°	17	16
75°	11	11
85°	4	5
90°	0	



TEST NUMBER: P1282988

CATALOG NUMBER: P3AS09R25B2750DE010 E3PHLP1MW_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	510.3
2.5°	502.7
5°	480.2
7.5°	445.2
10°	403.5
12.5°	358.5
15°	313.5
17.5°	270.1
20°	231.8
22.5°	196.8
25°	166.7
27.5°	140.1
30°	115.9
32.5°	95.0
35°	77.5
37.5°	61.7
40°	49.2
42.5°	39.2
45°	31.7
47.5°	27.5
50°	24.2
52.5°	22.5
55°	20.8
57.5°	20.0
60°	19.2
62.5°	17.5
65°	16.7
67.5°	15.0
70°	13.3
72.5°	12.5
75°	10.8
77.5°	9.2
80°	8.3
82.5°	6.7
85°	4.2
87.5°	1.7
90°	0.0

(END OF REPORT)