

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282176

Luminaire Tested: P3AS05R60B2750DE010 E3D1WH_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282176
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R60B2750DE010 E3D1WH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R60 optic, 5000K CCT AND, 80CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 509.0 lumens
Efficiency: N/A
Efficacy: 86.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282176

CATALOG NUMBER: P3AS05R60B2750DE010 E3D1WH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1282176

CATALOG NUMBER: P3AS05R60B2750DE010 E3D1WH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0				0				0
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94											94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88											88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82											82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77											77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72											72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67											67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63											63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59											59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56											56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53											53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	133367
5°	125908
10°	122621
15°	119819
20°	111403
25°	99586
30°	76088
35°	43928
40°	17032
45°	7102
50°	1569
55°	229
60°	175
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7102 cd/sqm

TEST NUMBER: P1282176

CATALOG NUMBER: P3AS05R60B2750DE010 E3D1WH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.0	10.6
10°-20°	147.0	28.9
20°-30°	184.1	36.2
30°-40°	102.9	20.2
40°-50°	19.6	3.8
50°-60°	1.0	0.2
60°-70°	0.2	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	385.2	75.7
0°-40°	488.1	95.9
0°-60°	508.7	99.9
0°-90°	509.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	509.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	608	
5°	572	54
15°	528	147
25°	412	184
35°	164	103
45°	23	20
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1282176

CATALOG NUMBER: P3AS05R60B2750DE010 E3D1WH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	608.2
1°	605.7
2°	597.8
3°	588.4
4°	579.7
5°	572.0
6°	566.1
7°	561.1
8°	557.4
9°	553.8
10°	550.7
11°	547.6
12°	544.1
13°	539.7
14°	534.5
15°	527.8
16°	519.7
17°	510.5
18°	500.1
19°	488.3
20°	477.4
21°	465.8
22°	453.7
23°	441.0
24°	427.0
25°	411.6
26°	393.5
27°	373.3
28°	350.6
29°	326.5
30°	300.5
31°	274.2
32°	247.2
32.5°	232.4
33°	219.0
34°	191.3
35°	164.1
36°	139.5
37°	113.5
37.5°	101.6
38°	89.9
39°	72.5
40°	59.5
42.5°	36.2
45°	22.9



TEST NUMBER: P1282176

CATALOG NUMBER: P3AS05R60B2750DE010 E3D1WH_5000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	12.7
50°	4.6
52.5°	1.0
55°	0.6
57.5°	0.4
60°	0.4
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)