

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282207

Luminaire Tested: P3AS05R60B2750DE010 E3DL1WMH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282207
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R60B2750DE010 E3DL1WMH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R60 optic, 2700K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 418.0 lumens
Efficiency: N/A
Efficacy: 70.9 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282207

CATALOG NUMBER: P3AS05R60B2750DE010 E3DL1WMH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1282207

CATALOG NUMBER: P3AS05R60B2750DE010 E3DL1WMH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86	83	80	79
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81	77	75	73
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76	72	69	68
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72	67	64	63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		67	63	60	59
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64	59	56	55
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60	56	53	51
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57	53	49	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	98698
5°	97777
10°	94921
15°	88922
20°	78710
25°	65834
30°	51603
35°	37423
40°	24904
45°	15536
50°	8392
55°	2447
60°	2281
65°	2075
70°	2052
75°	2033
80°	2020
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15536 cd/sqm

TEST NUMBER: P1282207

CATALOG NUMBER: P3AS05R60B2750DE010 E3DL1WMH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.8	10.0
10°-20°	108.7	26.0
20°-30°	123.9	29.6
30°-40°	87.8	21.0
40°-50°	39.8	9.5
50°-60°	8.5	2.0
60°-70°	4.1	1.0
70°-80°	2.5	0.6
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	274.4	65.6
0°-40°	362.2	86.6
0°-60°	410.5	98.2
0°-90°	418.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	418.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	450	
5°	444	42
15°	392	109
25°	272	124
35°	140	88
45°	50	40
55°	6	8
65°	4	4
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1282207

CATALOG NUMBER: P3AS05R60B2750DE010 E3DL1WMH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	450.1
2.5°	448.5
5°	444.2
7.5°	436.6
10°	426.3
12.5°	411.6
15°	391.7
17.5°	366.7
20°	337.3
22.5°	305.5
25°	272.1
27.5°	238.0
30°	203.8
32.5°	171.2
35°	139.8
37.5°	112.0
40°	87.0
42.5°	65.9
45°	50.1
47.5°	37.3
50°	24.6
52.5°	11.5
55°	6.4
57.5°	5.6
60°	5.2
62.5°	4.8
65°	4.0
67.5°	3.6
70°	3.2
72.5°	2.8
75°	2.4
77.5°	2.0
80°	1.6
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)