

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283058

Luminaire Tested: P3AS09R30B2750DE010 E3DL1LI_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283058
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R30B2750DE010 E3DL1LI_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 611.0 lumens
Efficiency: N/A
Efficacy: 46.6 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283058

CATALOG NUMBER: P3AS09R30B2750DE010 E3DL1LI_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1283058

CATALOG NUMBER: P3AS09R30B2750DE010 E3DL1LI_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	95	94	93	92	91	90	89	88
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	94	93	92	91	90	89	88	87	86	85	84
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	89	88	87	86	85	84	83	82	81	80	79
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	85	84	83	82	81	80	79	78	77	76	75
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	81	80	79	78	77	76	75	74	73	72	71
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	77	76	75	74	73	72	71	70	69	68	67
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	74	73	72	71	70	69	68	67	66	65	64
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	79	75	73	72	71	70	69	68	67	66	65	64	63	62	61
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	68	67	66	65	64	63	62	61	60	59	58
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	65	64	63	62	61	60	59	58	57	56	55
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	64	63	62	61	60	59	58	57	56	55	54	53

AVERAGE LUMINANCE (cd/sqm):

0°	356528
5°	339356
10°	285432
15°	205858
20°	127691
25°	72609
30°	40335
35°	21951
40°	11565
45°	6264
50°	3343
55°	2217
60°	2017
65°	2075
70°	1859
75°	1440
80°	1515
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6264 cd/sqm

TEST NUMBER: P1283058

CATALOG NUMBER: P3AS09R30B2750DE010 E3DL1LI_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.8	22.7
10°-20°	246.8	40.4
20°-30°	142.6	23.3
30°-40°	54.1	8.9
40°-50°	16.6	2.7
50°-60°	5.6	0.9
60°-70°	3.8	0.6
70°-80°	2.0	0.3
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	528.2	86.4
0°-40°	582.3	95.3
0°-60°	604.5	98.9
0°-90°	611.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	611.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1626	
5°	1542	139
15°	907	247
25°	300	143
35°	82	54
45°	20	17
55°	6	6
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1283058

CATALOG NUMBER: P3AS09R30B2750DE010 E3DL1LI_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1625.9
1°	1624.8
2°	1615.0
3°	1596.5
4°	1573.4
5°	1541.7
6°	1501.3
7°	1456.2
8°	1406.0
9°	1346.0
10°	1281.9
11°	1212.7
12°	1139.4
13°	1062.6
14°	984.7
15°	906.8
17.5°	715.1
20°	547.2
22.5°	405.8
25°	300.1
27.5°	218.2
30°	159.3
32.5°	114.9
35°	82.0
37.5°	57.1
40°	40.4
42.5°	28.3
45°	20.2
47.5°	13.9
50°	9.8
52.5°	6.9
55°	5.8
57.5°	5.2
60°	4.6
62.5°	4.0
65°	4.0
67.5°	3.5
70°	2.9
72.5°	2.3
75°	1.7
77.5°	1.7
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.0



TEST NUMBER: P1283058

CATALOG NUMBER: P3AS09R30B2750DE010 E3DL1LI_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)