

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282236

Luminaire Tested: P3AS05R60B2750DE010 E3DLD1WH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282236
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R60B2750DE010 E3DLD1WH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R60 optic, 5000K CCT AND, 80CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 349.9 lumens
Efficiency: N/A
Efficacy: 59.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282236

CATALOG NUMBER: P3AS05R60B2750DE010 E3DLD1WH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1282236

CATALOG NUMBER: P3AS05R60B2750DE010 E3DLD1WH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	98	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	71		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62122
5°	61435
10°	59295
15°	56028
20°	51641
25°	46769
30°	41525
35°	35469
40°	28224
45°	19878
50°	11872
55°	6002
60°	5789
65°	5292
70°	4873
75°	4660
80°	4293
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19878 cd/sqm

TEST NUMBER: P1282236

CATALOG NUMBER: P3AS05R60B2750DE010 E3DLD1WH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.2	7.5
10°-20°	69.0	19.7
20°-30°	88.6	25.3
30°-40°	82.1	23.5
40°-50°	50.0	14.3
50°-60°	16.6	4.8
60°-70°	10.1	2.9
70°-80°	5.7	1.6
80°-90°	1.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	183.8	52.5
0°-40°	265.9	76.0
0°-60°	332.5	95.0
0°-90°	349.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	349.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	283	
5°	279	26
15°	247	69
25°	193	89
35°	132	82
45°	64	50
55°	16	17
65°	10	10
75°	6	6
85°	1	2
90°	0	

TEST NUMBER: P1282236

CATALOG NUMBER: P3AS05R60B2750DE010 E3DLD1WH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	283.3
2.5°	282.1
5°	279.1
7.5°	273.6
10°	266.3
12.5°	257.4
15°	246.8
17.5°	234.5
20°	221.3
22.5°	207.3
25°	193.3
27.5°	178.8
30°	164.0
32.5°	149.1
35°	132.5
37.5°	115.1
40°	98.6
42.5°	81.1
45°	64.1
47.5°	49.7
50°	34.8
52.5°	20.8
55°	15.7
57.5°	14.4
60°	13.2
62.5°	11.5
65°	10.2
67.5°	8.9
70°	7.6
72.5°	6.4
75°	5.5
77.5°	4.2
80°	3.4
82.5°	2.1
85°	1.3
87.5°	0.8
90°	0.0

(END OF REPORT)