

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283136

Luminaire Tested: P3AS09R30B2750DE010 E3DLP1WMH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283136
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R30B2750DE010 E3DLP1WMH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 5000K CCT AND, 80CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 404.1 lumens
Efficiency: N/A
Efficacy: 30.8 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283136

CATALOG NUMBER: P3AS09R30B2750DE010 E3DLP1WMH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1283136

CATALOG NUMBER: P3AS09R30B2750DE010 E3DLP1WMH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	74	68	64	72	67	63		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	67	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	58	54	72	63	57	54	62	57	53		61	57	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	138059
5°	133766
10°	120505
15°	99683
20°	77193
25°	57899
30°	42032
35°	28001
40°	17204
45°	10110
50°	6209
55°	5046
60°	4386
65°	3580
70°	3206
75°	3219
80°	2399
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10110 cd/sqm

TEST NUMBER: P1283136

CATALOG NUMBER: P3AS09R30B2750DE010 E3DLP1WMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.9	13.8
10°-20°	120.9	29.9
20°-30°	110.0	27.2
30°-40°	66.5	16.5
40°-50°	26.7	6.6
50°-60°	11.8	2.9
60°-70°	7.1	1.8
70°-80°	3.9	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	286.9	71.0
0°-40°	353.4	87.5
0°-60°	391.9	97.0
0°-90°	404.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	404.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	630	
5°	608	56
15°	439	121
25°	239	110
35°	105	67
45°	33	27
55°	13	12
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1283136

CATALOG NUMBER: P3AS09R30B2750DE010 E3DLP1WMH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	629.6
1°	629.0
2°	626.4
3°	622.1
4°	615.8
5°	607.7
6°	597.6
7°	587.0
8°	573.2
9°	557.5
10°	541.2
11°	522.5
12°	502.4
13°	482.4
14°	460.4
15°	439.1
17.5°	383.4
20°	330.8
22.5°	281.9
25°	239.3
27.5°	200.5
30°	166.0
32.5°	134.1
35°	104.6
37.5°	80.2
40°	60.1
42.5°	43.9
45°	32.6
47.5°	24.4
50°	18.2
52.5°	14.4
55°	13.2
57.5°	11.3
60°	10.0
62.5°	8.1
65°	6.9
67.5°	6.3
70°	5.0
72.5°	4.4
75°	3.8
77.5°	3.1
80°	1.9
82.5°	1.3
85°	1.3
87.5°	0.6



TEST NUMBER: P1283136

CATALOG NUMBER: P3AS09R30B2750DE010 E3DLP1WMH_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)