

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283145

Luminaire Tested: P3AS09R30B2750DE010 E3PHLD1MW_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283145
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R30B2750DE010 E3PHLD1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 4000K CCT AND, 80CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 455.9 lumens
Efficiency: N/A
Efficacy: 34.8 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283145

CATALOG NUMBER: P3AS09R30B2750DE010 E3PHLD1MW_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1283145

CATALOG NUMBER: P3AS09R30B2750DE010 E3PHLD1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		94	93	91	90
2	104	98	93	88	102	96	91	87	93	89	85		90	86	83		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	76	73	71
4	91	82	75	69	89	80	74	69	78	72	68		76	71	67		74	70	66	65
5	85	75	68	63	84	74	67	62	72	66	62		70	65	61		69	64	61	59
6	80	69	62	57	79	69	62	57	67	61	56		65	60	56		64	59	56	54
7	76	65	57	52	74	64	57	52	62	56	52		61	56	52		60	55	51	50
8	71	60	53	48	70	60	53	48	58	52	48		57	52	48		56	51	48	46
9	68	57	50	45	66	56	49	45	55	49	45		54	49	45		53	48	44	43
10	64	53	47	42	63	53	46	42	52	46	42		51	46	42		50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	112359
5°	107396
10°	92628
15°	76777
20°	62935
25°	50737
30°	40892
35°	33488
40°	27824
45°	23599
50°	20195
55°	17471
60°	15569
65°	13594
70°	11925
75°	9997
80°	7450
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23599 cd/sqm

TEST NUMBER: P1283145

CATALOG NUMBER: P3AS09R30B2750DE010 E3PHLD1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.2	9.7
10°-20°	94.3	20.7
20°-30°	96.7	21.2
30°-40°	79.0	17.3
40°-50°	59.1	13.0
50°-60°	41.5	9.1
60°-70°	26.1	5.7
70°-80°	12.6	2.8
80°-90°	2.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	235.2	51.6
0°-40°	314.2	68.9
0°-60°	414.9	91.0
0°-90°	455.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	455.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	512	
5°	488	44
15°	338	94
25°	210	97
35°	125	79
45°	76	59
55°	46	42
65°	26	26
75°	12	13
85°	2	2
90°	0	

TEST NUMBER: P1283145

CATALOG NUMBER: P3AS09R30B2750DE010 E3PHLD1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	512.4
2.5°	507.4
5°	487.9
7.5°	455.8
10°	416.0
12.5°	377.1
15°	338.2
17.5°	302.7
20°	269.7
22.5°	238.5
25°	209.7
27.5°	184.3
30°	161.5
32.5°	142.9
35°	125.1
37.5°	110.8
40°	97.2
42.5°	86.2
45°	76.1
47.5°	66.8
50°	59.2
52.5°	52.4
55°	45.7
57.5°	40.6
60°	35.5
62.5°	30.4
65°	26.2
67.5°	22.0
70°	18.6
72.5°	15.2
75°	11.8
77.5°	8.5
80°	5.9
82.5°	3.4
85°	1.7
87.5°	0.8
90°	0.0

(END OF REPORT)