

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282323

Luminaire Tested: P3AS05R65B2750DE010 E3D1WMH_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282323
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R65B2750DE010 E3D1WMH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 467.0 lumens
Efficiency: N/A
Efficacy: 79.2 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282323

CATALOG NUMBER: P3AS05R65B2750DE010 E3D1WMH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1282323

CATALOG NUMBER: P3AS05R65B2750DE010 E3D1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75
7	84	75	70	65	83	75	69	65	73	69	65		72	68	65		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	67	61	58	76	67	61	57	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125143
5°	116200
10°	112356
15°	108287
20°	100109
25°	91215
30°	70467
35°	40850
40°	16202
45°	6915
50°	1637
55°	229
60°	175
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6915 cd/sqm

TEST NUMBER: P1282323

CATALOG NUMBER: P3AS05R65B2750DE010 E3D1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.8	10.7
10°-20°	132.9	28.5
20°-30°	168.2	36.0
30°-40°	95.8	20.5
40°-50°	19.0	4.1
50°-60°	1.0	0.2
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	350.9	75.1
0°-40°	446.7	95.6
0°-60°	466.7	99.9
0°-90°	467.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	467.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	571	
5°	528	50
15°	477	133
25°	377	168
35°	153	96
45°	22	19
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1282323

CATALOG NUMBER: P3AS05R65B2750DE010 E3D1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	570.7
1°	566.4
2°	557.2
3°	546.5
4°	535.9
5°	527.9
6°	521.9
7°	517.1
8°	512.9
9°	508.7
10°	504.6
11°	500.2
12°	495.6
13°	490.0
14°	484.1
15°	477.0
16°	468.5
17°	459.3
18°	449.4
19°	438.8
20°	429.0
21°	419.0
22°	410.0
23°	400.6
24°	389.7
25°	377.0
26°	361.8
27°	343.6
28°	323.1
29°	301.2
30°	278.3
31°	253.2
32°	228.2
32.5°	215.4
33°	202.9
34°	177.6
35°	152.6
36°	129.6
37°	106.7
37.5°	95.0
38°	85.6
39°	69.3
40°	56.6
42.5°	34.9
45°	22.3



TEST NUMBER: P1282323

CATALOG NUMBER: P3AS05R65B2750DE010 E3D1WMH_3000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	13.1
50°	4.8
52.5°	1.0
55°	0.6
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)