

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283200

Luminaire Tested: P3AS09R35B2750DE010 E3DL1LI\_4000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1283200  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R35B2750DE010 E3DL1LI\_4000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 4000K CCT AND, 80CRI , E3DL1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 617.0 lumens  
Efficiency: N/A  
Efficacy: 47.1 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 13.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1283200  
CATALOG NUMBER: P3AS09R35B2750DE010 E3DL1LI\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1283200  
 CATALOG NUMBER: P3AS09R35B2750DE010 E3DL1LI\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	82	82	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	78	78	78	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	74	74	74	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	71	71	71	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	68	68	68	66
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	67	65	65	65	65	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	62	62	62	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	311181
5°	299075
10°	260583
15°	199593
20°	133525
25°	80787
30°	46362
35°	25913
40°	13769
45°	7102
50°	3411
55°	2676
60°	2588
65°	2127
70°	2244
75°	1949
80°	2273
85°	1510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7102 cd/sqm



TEST NUMBER: P1283200  
 CATALOG NUMBER: P3AS09R35B2750DE010 E3DL1LI\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	123.6	20.0
10°-20°	239.6	38.8
20°-30°	156.8	25.4
30°-40°	63.6	10.3
40°-50°	19.1	3.1
50°-60°	6.5	1.1
60°-70°	4.3	0.7
70°-80°	2.5	0.4
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	520.0	84.3
0°-40°	583.6	94.6
0°-60°	609.2	98.7
0°-90°	617.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	617.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1419	
5°	1359	124
15°	879	240
25°	334	157
35°	97	64
45°	23	19
55°	7	6
65°	4	4
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1283200  
CATALOG NUMBER: P3AS09R35B2750DE010 E3DL1LI\_4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1419.1
1°	1416.8
2°	1410.3
3°	1397.4
4°	1382.2
5°	1358.7
6°	1329.3
7°	1296.5
8°	1259.5
9°	1217.2
10°	1170.3
11°	1118.0
12°	1063.5
13°	1002.4
14°	944.3
15°	879.2
17.5°	721.3
20°	572.2
22.5°	440.2
25°	333.9
27.5°	248.8
30°	183.1
32.5°	134.4
35°	96.8
37.5°	68.7
40°	48.1
42.5°	33.5
45°	22.9
47.5°	15.3
50°	10.0
52.5°	7.6
55°	7.0
57.5°	6.5
60°	5.9
62.5°	5.3
65°	4.1
67.5°	3.5
70°	3.5
72.5°	2.9
75°	2.3
77.5°	1.8
80°	1.8
82.5°	1.2
85°	0.6
87.5°	0.6



TEST NUMBER: P1283200  
CATALOG NUMBER: P3AS09R35B2750DE010 E3DL1LI\_4000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)