

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282380

Luminaire Tested: P3AS05R65B2750DE010 E3DLD1WH\_4000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1282380  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R65B2750DE010 E3DLD1WH\_4000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 4000K CCT AND, 80CRI , E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 314.1 lumens  
Efficiency: N/A  
Efficacy: 53.2 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1282380

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLD1WH\_4000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1282380

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLD1WH\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |  |  |  |    |  |  |  |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|--|--|--|----|--|--|--|----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    | 20 |  |  |  | 20 |  |  |  | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    |    | 0  |  |  |  | 0  |  |  |  | 0  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0  |  |  |  | 0  |  |  |  | 0  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |  |  |  |    |  |  |  |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |    |  |  |  |    |  |  |  |    |
| 1   | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 101 | 102 | 100 | 98  | 99  | 97  | 95  | 95  | 94  | 93  | 91  |    |    |    |  |  |  |    |  |  |  |    |
| 2   | 105 | 99  | 94  | 90  | 103 | 97  | 93  | 89  | 94  | 90  | 87  | 91  | 88  | 85  | 88  | 86  | 84  | 82  |    |    |    |  |  |  |    |  |  |  |    |
| 3   | 99  | 91  | 85  | 80  | 96  | 89  | 84  | 79  | 87  | 82  | 78  | 84  | 80  | 77  | 82  | 78  | 76  | 74  |    |    |    |  |  |  |    |  |  |  |    |
| 4   | 92  | 83  | 77  | 72  | 90  | 82  | 76  | 71  | 80  | 75  | 70  | 78  | 73  | 70  | 76  | 72  | 69  | 67  |    |    |    |  |  |  |    |  |  |  |    |
| 5   | 87  | 77  | 70  | 65  | 85  | 76  | 69  | 65  | 74  | 68  | 64  | 72  | 67  | 63  | 71  | 66  | 63  | 61  |    |    |    |  |  |  |    |  |  |  |    |
| 6   | 82  | 71  | 64  | 59  | 80  | 70  | 64  | 59  | 69  | 63  | 58  | 67  | 62  | 58  | 66  | 61  | 58  | 56  |    |    |    |  |  |  |    |  |  |  |    |
| 7   | 77  | 66  | 59  | 54  | 75  | 65  | 59  | 54  | 64  | 58  | 54  | 63  | 57  | 53  | 61  | 57  | 53  | 51  |    |    |    |  |  |  |    |  |  |  |    |
| 8   | 72  | 61  | 55  | 50  | 71  | 61  | 54  | 50  | 60  | 54  | 49  | 59  | 53  | 49  | 58  | 53  | 49  | 47  |    |    |    |  |  |  |    |  |  |  |    |
| 9   | 68  | 57  | 51  | 46  | 67  | 57  | 50  | 46  | 56  | 50  | 46  | 55  | 49  | 46  | 54  | 49  | 45  | 44  |    |    |    |  |  |  |    |  |  |  |    |
| 10  | 65  | 54  | 47  | 43  | 64  | 53  | 47  | 43  | 52  | 47  | 43  | 52  | 46  | 42  | 51  | 46  | 42  | 41  |    |    |    |  |  |  |    |  |  |  |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 55873 |
| 5°  | 55118 |
| 10° | 53283 |
| 15° | 50239 |
| 20° | 46344 |
| 25° | 42075 |
| 30° | 37272 |
| 35° | 31695 |
| 40° | 25219 |
| 45° | 17800 |
| 50° | 10337 |
| 55° | 5658  |
| 60° | 5263  |
| 65° | 4774  |
| 70° | 4360  |
| 75° | 4067  |
| 80° | 3536  |
| 85° | 3019  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17800 cd/sqm

TEST NUMBER: P1282380

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLD1WH\_4000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 23.6   | 7.5       |
| 10°-20°   | 61.9   | 19.7      |
| 20°-30°   | 79.6   | 25.3      |
| 30°-40°   | 73.6   | 23.4      |
| 40°-50°   | 44.4   | 14.1      |
| 50°-60°   | 15.2   | 4.8       |
| 60°-70°   | 9.1    | 2.9       |
| 70°-80°   | 5.2    | 1.6       |
| 80°-90°   | 1.5    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 165.1  | 52.6      |
| 0°-40°    | 238.7  | 76.0      |
| 0°-60°    | 298.3  | 95.0      |
| 0°-90°    | 314.1  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 314.1  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 255 |      |
| 5°  | 250 | 24   |
| 15° | 221 | 62   |
| 25° | 174 | 80   |
| 35° | 118 | 74   |
| 45° | 57  | 44   |
| 55° | 15  | 15   |
| 65° | 9   | 9    |
| 75° | 5   | 5    |
| 85° | 1   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1282380

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLD1WH\_4000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 254.8 |
| 2.5°  | 253.6 |
| 5°    | 250.4 |
| 7.5°  | 245.7 |
| 10°   | 239.3 |
| 12.5° | 231.3 |
| 15°   | 221.3 |
| 17.5° | 210.6 |
| 20°   | 198.6 |
| 22.5° | 186.2 |
| 25°   | 173.9 |
| 27.5° | 160.7 |
| 30°   | 147.2 |
| 32.5° | 133.6 |
| 35°   | 118.4 |
| 37.5° | 103.7 |
| 40°   | 88.1  |
| 42.5° | 72.6  |
| 45°   | 57.4  |
| 47.5° | 43.5  |
| 50°   | 30.3  |
| 52.5° | 19.1  |
| 55°   | 14.8  |
| 57.5° | 13.2  |
| 60°   | 12.0  |
| 62.5° | 10.4  |
| 65°   | 9.2   |
| 67.5° | 8.0   |
| 70°   | 6.8   |
| 72.5° | 6.0   |
| 75°   | 4.8   |
| 77.5° | 4.0   |
| 80°   | 2.8   |
| 82.5° | 2.0   |
| 85°   | 1.2   |
| 87.5° | 0.8   |
| 90°   | 0.0   |

(END OF REPORT)