

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282382

Luminaire Tested: P3AS05R65B2750DE010 E3DLD1WMH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282382
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R65B2750DE010 E3DLD1WMH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 2700K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 313.0 lumens
Efficiency: N/A
Efficacy: 53.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282382

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLD1WMH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1282382

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLD1WMH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0				0				0
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91											
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82											
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74											
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67											
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61											
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56											
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51											
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47											
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44											
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55697
5°	54942
10°	53105
15°	50080
20°	46204
25°	41930
30°	37145
35°	31614
40°	25161
45°	17738
50°	10302
55°	5620
60°	5219
65°	4722
70°	4360
75°	4067
80°	3536
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17738 cd/sqm

TEST NUMBER: P1282382

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLD1WMH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.5	7.5
10°-20°	61.7	19.7
20°-30°	79.3	25.3
30°-40°	73.4	23.4
40°-50°	44.3	14.1
50°-60°	15.1	4.8
60°-70°	9.1	2.9
70°-80°	5.2	1.7
80°-90°	1.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	164.5	52.6
0°-40°	237.9	76.0
0°-60°	297.3	95.0
0°-90°	313.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	313.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	254	
5°	250	23
15°	221	62
25°	173	79
35°	118	73
45°	57	44
55°	15	15
65°	9	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1282382

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLD1WMH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	254.0
2.5°	252.8
5°	249.6
7.5°	244.9
10°	238.5
12.5°	230.6
15°	220.6
17.5°	209.9
20°	198.0
22.5°	185.6
25°	173.3
27.5°	160.2
30°	146.7
32.5°	133.2
35°	118.1
37.5°	103.4
40°	87.9
42.5°	72.3
45°	57.2
47.5°	43.3
50°	30.2
52.5°	19.1
55°	14.7
57.5°	13.1
60°	11.9
62.5°	10.3
65°	9.1
67.5°	8.0
70°	6.8
72.5°	6.0
75°	4.8
77.5°	4.0
80°	2.8
82.5°	2.0
85°	1.2
87.5°	0.8
90°	0.0

(END OF REPORT)