

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282388

Luminaire Tested: P3AS05R65B2750DE010 E3DLP1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282388
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R65B2750DE010 E3DLP1GPH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 133.1 lumens
Efficiency: N/A
Efficacy: 22.6 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282388

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLP1GPH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1282388

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLP1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		90
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	64	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	63	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	33813
5°	32974
10°	30705
15°	27514
20°	23755
25°	19767
30°	15597
35°	11538
40°	7958
45°	4931
50°	2695
55°	1682
60°	1447
65°	1297
70°	1090
75°	1017
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4931 cd/sqm

TEST NUMBER: P1282388

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLP1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.9	10.5
10°-20°	33.7	25.3
20°-30°	37.2	28.0
30°-40°	27.1	20.3
40°-50°	12.7	9.5
50°-60°	4.3	3.2
60°-70°	2.5	1.9
70°-80°	1.3	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	84.8	63.8
0°-40°	111.9	84.1
0°-60°	128.8	96.8
0°-90°	133.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	133.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	154	
5°	150	14
15°	121	34
25°	82	37
35°	43	27
45°	16	13
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1282388

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLP1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	154.2
2.5°	153.2
5°	149.8
7.5°	144.6
10°	137.9
12.5°	130.0
15°	121.2
17.5°	111.6
20°	101.8
22.5°	91.7
25°	81.7
27.5°	71.5
30°	61.6
32.5°	52.0
35°	43.1
37.5°	35.1
40°	27.8
42.5°	21.3
45°	15.9
47.5°	11.5
50°	7.9
52.5°	5.4
55°	4.4
57.5°	3.8
60°	3.3
62.5°	2.9
65°	2.5
67.5°	2.1
70°	1.7
72.5°	1.5
75°	1.2
77.5°	1.0
80°	0.8
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)