

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282438

Luminaire Tested: P3AS05R70B2750DE010 E3CD1MMS_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282438
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R70B2750DE010 E3CD1MMS_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 3000K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 489.1 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282438

CATALOG NUMBER: P3AS05R70B2750DE010 E3CD1MMS_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1282438

CATALOG NUMBER: P3AS05R70B2750DE010 E3CD1MMS_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	82	80	78
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80	77	74	72
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75	71	68	66
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70	66	63	61
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66	62	58	57
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62	57	54	53
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58	54	50	49
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55	50	47	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97097
5°	92648
10°	88152
15°	85789
20°	82631
25°	78198
30°	72745
35°	61114
40°	39388
45°	18296
50°	4810
55°	1185
60°	1184
65°	1038
70°	1026
75°	1017
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18296 cd/sqm

TEST NUMBER: P1282438

CATALOG NUMBER: P3AS05R70B2750DE010 E3CD1MMS_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.4	8.1
10°-20°	106.2	21.7
20°-30°	148.4	30.3
30°-40°	137.6	28.1
40°-50°	49.3	10.1
50°-60°	4.2	0.9
60°-70°	2.1	0.4
70°-80°	1.4	0.3
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	294.0	60.1
0°-40°	431.6	88.2
0°-60°	485.0	99.2
0°-90°	489.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	489.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	443	
5°	421	39
15°	378	106
25°	323	148
35°	228	138
45°	59	49
55°	3	4
65°	2	2
75°	1	1
85°	0	1
90°	0	



TEST NUMBER: P1282438

CATALOG NUMBER: P3AS05R70B2750DE010 E3CD1MMS_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	442.8
2.5°	436.2
5°	420.9
7.5°	406.9
10°	395.9
12.5°	386.9
15°	377.9
17.5°	367.0
20°	354.1
22.5°	339.2
25°	323.2
27.5°	306.8
30°	287.3
32.5°	262.3
35°	228.3
37.5°	184.9
40°	137.6
42.5°	93.8
45°	59.0
47.5°	32.8
50°	14.1
52.5°	4.7
55°	3.1
57.5°	2.7
60°	2.7
62.5°	2.3
65°	2.0
67.5°	2.0
70°	1.6
72.5°	1.6
75°	1.2
77.5°	1.2
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)