

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282450

Luminaire Tested: P3AS05R70B2750DE010 E3D1H_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282450
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R70B2750DE010 E3D1H_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 4000K CCT AND, 80CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 475.0 lumens
Efficiency: N/A
Efficacy: 80.5 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282450
CATALOG NUMBER: P3AS05R70B2750DE010 E3D1H_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1282450
 CATALOG NUMBER: P3AS05R70B2750DE010 E3D1H_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79			79
4	95	87	81	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72			72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57			57
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	92361
5°	87079
10°	82586
15°	81090
20°	78173
25°	73674
30°	73150
35°	63711
40°	41220
45°	19475
50°	2729
55°	229
60°	175
65°	208
70°	128
75°	169
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19475 cd/sqm



TEST NUMBER: P1282450
 CATALOG NUMBER: P3AS05R70B2750DE010 E3D1H_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.9	7.8
10°-20°	100.3	21.1
20°-30°	141.9	29.9
30°-40°	142.6	30.0
40°-50°	51.3	10.8
50°-60°	1.4	0.3
60°-70°	0.3	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	279.2	58.8
0°-40°	421.8	88.8
0°-60°	474.5	99.9
0°-90°	475.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	475.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	421	
5°	396	37
15°	357	100
25°	304	142
35°	238	143
45°	63	51
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1282450
CATALOG NUMBER: P3AS05R70B2750DE010 E3D1H_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	421.2
1°	420.0
2°	416.3
3°	410.5
4°	403.1
5°	395.6
6°	388.6
7°	383.2
8°	378.3
9°	374.4
10°	370.9
11°	367.9
12°	365.2
13°	362.5
14°	359.9
15°	357.2
16°	353.9
17°	350.4
18°	346.1
19°	340.8
20°	335.0
21°	328.5
22°	322.1
23°	315.8
24°	309.8
25°	304.5
26°	300.8
27°	297.9
28°	295.6
29°	292.8
30°	288.9
31°	283.3
32°	275.3
32.5°	270.8
33°	264.7
34°	252.8
35°	238.0
36°	221.6
37°	203.1
37.5°	194.5
38°	182.8
39°	161.9
40°	144.0
42.5°	99.7
45°	62.8



TEST NUMBER: P1282450
CATALOG NUMBER: P3AS05R70B2750DE010 E3D1H_4000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	33.8
50°	8.0
52.5°	1.0
55°	0.6
57.5°	0.6
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.2
77.5°	0.2
80°	0.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)