

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283361

Luminaire Tested: P3AS09R40B2750DE010 E3DL1LI_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283361
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R40B2750DE010 E3DL1LI_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 5000K CCT AND, 80CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 730.0 lumens
Efficiency: N/A
Efficacy: 55.7 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283361

CATALOG NUMBER: P3AS09R40B2750DE010 E3DL1LI_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1283361

CATALOG NUMBER: P3AS09R40B2750DE010 E3DL1LI_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	96	96	94
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	91	91	89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	86	86	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	81	81	80
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	67	67	65
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	64	64	63
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	61	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	323022
5°	313625
10°	284608
15°	235121
20°	169601
25°	104909
30°	56794
35°	29366
40°	15973
45°	8931
50°	4503
55°	3364
60°	3026
65°	2906
70°	2821
75°	2626
80°	2399
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8931 cd/sqm

TEST NUMBER: P1283361

CATALOG NUMBER: P3AS09R40B2750DE010 E3DL1LI_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.3	18.0
10°-20°	282.0	38.6
20°-30°	201.3	27.6
30°-40°	74.1	10.2
40°-50°	23.3	3.2
50°-60°	8.1	1.1
60°-70°	5.6	0.8
70°-80°	3.3	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	614.6	84.2
0°-40°	688.7	94.3
0°-60°	720.2	98.7
0°-90°	730.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	730.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1473	
5°	1425	131
15°	1036	282
25°	434	201
35°	110	74
45°	29	23
55°	9	8
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1283361

CATALOG NUMBER: P3AS09R40B2750DE010 E3DL1LI_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1473.1
2.5°	1461.8
5°	1424.8
7.5°	1363.4
10°	1278.2
12.5°	1169.8
15°	1035.7
17.5°	885.4
20°	726.8
22.5°	570.8
25°	433.6
27.5°	318.3
30°	224.3
32.5°	157.3
35°	109.7
37.5°	77.7
40°	55.8
42.5°	40.1
45°	28.8
47.5°	19.4
50°	13.2
52.5°	9.4
55°	8.8
57.5°	8.1
60°	6.9
62.5°	6.3
65°	5.6
67.5°	5.0
70°	4.4
72.5°	3.8
75°	3.1
77.5°	2.5
80°	1.9
82.5°	1.3
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)