

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282452

Luminaire Tested: P3AS05R70B2750DE010 E3D1LI_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282452
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R70B2750DE010 E3D1LI_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 2700K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 474.0 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282452

CATALOG NUMBER: P3AS05R70B2750DE010 E3D1LI_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1282452

CATALOG NUMBER: P3AS05R70B2750DE010 E3D1LI_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		86	83	80	79
4	95	87	81	77	94	86	81	77	84	79	76		82	78	75		80	77	74	72
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75	71	68	66
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70	66	63	61
7	80	70	64	59	79	70	63	59	68	63	59		67	62	58		66	61	58	57
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58	53	50	49
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55	50	47	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	92164
5°	86903
10°	82408
15°	80931
20°	78010
25°	73528
30°	72999
35°	63577
40°	41134
45°	19444
50°	2729
55°	229
60°	175
65°	208
70°	128
75°	169
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19444 cd/sqm

TEST NUMBER: P1282452

CATALOG NUMBER: P3AS05R70B2750DE010 E3D1LI_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.9	7.8
10°-20°	100.1	21.1
20°-30°	141.6	29.9
30°-40°	142.3	30.0
40°-50°	51.2	10.8
50°-60°	1.4	0.3
60°-70°	0.3	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	278.6	58.8
0°-40°	420.9	88.8
0°-60°	473.5	99.9
0°-90°	474.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	474.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	420	
5°	395	37
15°	356	100
25°	304	142
35°	238	142
45°	63	51
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1282452

CATALOG NUMBER: P3AS05R70B2750DE010 E3D1LI_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	420.3
1°	419.1
2°	415.4
3°	409.6
4°	402.2
5°	394.8
6°	387.8
7°	382.3
8°	377.5
9°	373.6
10°	370.1
11°	367.2
12°	364.4
13°	361.7
14°	359.2
15°	356.5
16°	353.1
17°	349.6
18°	345.4
19°	340.1
20°	334.3
21°	327.8
22°	321.4
23°	315.2
24°	309.1
25°	303.9
26°	300.2
27°	297.3
28°	294.9
29°	292.2
30°	288.3
31°	282.7
32°	274.7
32.5°	270.2
33°	264.2
34°	252.3
35°	237.5
36°	221.2
37°	202.7
37.5°	194.1
38°	182.4
39°	161.6
40°	143.7
42.5°	99.5
45°	62.7



TEST NUMBER: P1282452

CATALOG NUMBER: P3AS05R70B2750DE010 E3D1LI_2700K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	33.7
50°	8.0
52.5°	1.0
55°	0.6
57.5°	0.6
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.2
77.5°	0.2
80°	0.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)