

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283377

Luminaire Tested: P3AS09R40B2750DE010 E3DLD1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283377
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R40B2750DE010 E3DLD1GPH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 2700K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 256.0 lumens
Efficiency: N/A
Efficacy: 19.5 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283377

CATALOG NUMBER: P3AS09R40B2750DE010 E3DLD1GPH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1283377

CATALOG NUMBER: P3AS09R40B2750DE010 E3DLD1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	57473
5°	56416
10°	53194
15°	48309
20°	42447
25°	36244
30°	30030
35°	23155
40°	16488
45°	11102
50°	6072
55°	4282
60°	4035
65°	3736
70°	3334
75°	3135
80°	2526
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11102 cd/sqm

TEST NUMBER: P1283377

CATALOG NUMBER: P3AS09R40B2750DE010 E3DLD1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.9	9.3
10°-20°	59.3	23.2
20°-30°	68.5	26.8
30°-40°	54.0	21.1
40°-50°	27.7	10.8
50°-60°	10.6	4.1
60°-70°	7.0	2.7
70°-80°	3.8	1.5
80°-90°	1.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	151.7	59.3
0°-40°	205.7	80.3
0°-60°	244.1	95.3
0°-90°	256.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	256.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	262	
5°	256	24
15°	213	59
25°	150	69
35°	86	54
45°	36	28
55°	11	11
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1283377

CATALOG NUMBER: P3AS09R40B2750DE010 E3DLD1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	262.1
2.5°	260.6
5°	256.3
7.5°	248.9
10°	238.9
12.5°	227.1
15°	212.8
17.5°	197.9
20°	181.9
22.5°	165.5
25°	149.8
27.5°	134.0
30°	118.6
32.5°	102.8
35°	86.5
37.5°	71.3
40°	57.6
42.5°	45.8
45°	35.8
47.5°	26.1
50°	17.8
52.5°	12.9
55°	11.2
57.5°	10.0
60°	9.2
62.5°	8.0
65°	7.2
67.5°	6.0
70°	5.2
72.5°	4.3
75°	3.7
77.5°	2.9
80°	2.0
82.5°	1.7
85°	0.9
87.5°	0.6
90°	0.0

(END OF REPORT)