

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282524

Luminaire Tested: P3AS05R70B2750DE010 E3DLP1WH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282524
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R70B2750DE010 E3DLP1WH_3500K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 3500K CCT AND, 80CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 404.0 lumens
Efficiency: N/A
Efficacy: 68.5 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282524

CATALOG NUMBER: P3AS05R70B2750DE010 E3DLP1WH_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1282524

CATALOG NUMBER: P3AS05R70B2750DE010 E3DLP1WH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96	95	94		92
2	106	101	96	93	104	99	95	92	96	93	90		93	90	88		90	88	86		84
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84	81	79		77
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79	75	72		70
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74	70	66		65
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69	65	61		60
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65	60	57		55
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61	56	53		51
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57	52	49		48
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54	49	46		44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	78217
5°	77284
10°	75038
15°	71851
20°	67323
25°	61165
30°	52818
35°	42108
40°	30657
45°	20157
50°	9450
55°	2906
60°	2807
65°	2698
70°	2565
75°	2711
80°	2526
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 20157 cd/sqm

TEST NUMBER: P1282524

CATALOG NUMBER: P3AS05R70B2750DE010 E3DLP1WH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.1	8.2
10°-20°	88.6	21.9
20°-30°	115.1	28.5
30°-40°	97.7	24.2
40°-50°	50.4	12.5
50°-60°	9.7	2.4
60°-70°	5.2	1.3
70°-80°	3.2	0.8
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	236.8	58.6
0°-40°	334.5	82.8
0°-60°	394.6	97.7
0°-90°	404.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	404.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	357	
5°	351	33
15°	316	89
25°	253	115
35°	157	98
45°	65	50
55°	8	10
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1282524

CATALOG NUMBER: P3AS05R70B2750DE010 E3DLP1WH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	356.7
2.5°	355.5
5°	351.1
7.5°	344.6
10°	337.0
12.5°	327.4
15°	316.5
17.5°	303.3
20°	288.5
22.5°	271.6
25°	252.8
27.5°	231.5
30°	208.6
32.5°	183.3
35°	157.3
37.5°	131.6
40°	107.1
42.5°	84.3
45°	65.0
47.5°	47.7
50°	27.7
52.5°	12.0
55°	7.6
57.5°	7.2
60°	6.4
62.5°	6.0
65°	5.2
67.5°	4.8
70°	4.0
72.5°	3.6
75°	3.2
77.5°	2.4
80°	2.0
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)