

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282527

Luminaire Tested: P3AS05R70B2750DE010 E3DLP1WMH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282527
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R70B2750DE010 E3DLP1WMH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 2700K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 285.0 lumens
Efficiency: N/A
Efficacy: 48.3 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282527
CATALOG NUMBER: P3AS05R70B2750DE010 E3DLP1WMH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1282527

CATALOG NUMBER: P3AS05R70B2750DE010 E3DLP1WMH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84				84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77				77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71				71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65				65
6	85	75	68	64	83	74	68	63	73	67	63	71	66	63	70	65	62	61				61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56				56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49				49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46				46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	66859
5°	65617
10°	61878
15°	56164
20°	49121
25°	41446
30°	33929
35°	26314
40°	18835
45°	11939
50°	5936
55°	3632
60°	3114
65°	2906
70°	2565
75°	2372
80°	2020
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11939 cd/sqm



TEST NUMBER: P1282527

CATALOG NUMBER: P3AS05R70B2750DE010 E3DLP1WMH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.8	9.8
10°-20°	68.8	24.1
20°-30°	78.4	27.5
30°-40°	61.3	21.5
40°-50°	30.1	10.6
50°-60°	9.2	3.2
60°-70°	5.5	1.9
70°-80°	3.0	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	175.0	61.4
0°-40°	236.4	82.9
0°-60°	275.7	96.7
0°-90°	285.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	285.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	305	
5°	298	28
15°	247	69
25°	171	78
35°	98	61
45°	38	30
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1282527
CATALOG NUMBER: P3AS05R70B2750DE010 E3DLP1WMH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	304.9
2.5°	303.3
5°	298.1
7.5°	289.8
10°	277.9
12.5°	264.0
15°	247.4
17.5°	229.5
20°	210.5
22.5°	190.7
25°	171.3
27.5°	152.2
30°	134.0
32.5°	115.8
35°	98.3
37.5°	81.7
40°	65.8
42.5°	51.1
45°	38.5
47.5°	27.0
50°	17.4
52.5°	11.5
55°	9.5
57.5°	8.3
60°	7.1
62.5°	6.3
65°	5.6
67.5°	4.8
70°	4.0
72.5°	3.2
75°	2.8
77.5°	2.4
80°	1.6
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)