

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282568

Luminaire Tested: P3AS09R15B2750DE010 E3CD1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282568
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R15B2750DE010 E3CD1MW_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3CD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 730.1 lumens
Efficiency: N/A
Efficacy: 55.7 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282568

CATALOG NUMBER: P3AS09R15B2750DE010 E3CD1MW_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1282568

CATALOG NUMBER: P3AS09R15B2750DE010 E3CD1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98		
2	113	110	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96		
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	97	95	94		
4	107	103	100	97	106	102	99	97	100	97	95	98	96	94	97	95	93	92		
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92	91		
6	103	98	94	92	102	97	94	92	96	93	91	95	92	91	94	92	90	89		
7	101	96	92	90	100	95	92	90	94	91	89	93	91	89	92	90	89	88		
8	99	94	90	88	98	93	90	88	92	90	88	92	89	87	91	89	87	86		
9	97	92	89	87	97	92	89	86	91	88	86	90	88	86	90	87	86	85		
10	96	90	87	85	95	90	87	85	89	87	85	89	86	85	88	86	85	84		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1418943
5°	1189211
10°	560177
15°	168877
20°	62492
25°	24292
30°	9065
35°	2784
40°	1002
45°	527
50°	409
55°	459
60°	526
65°	311
70°	385
75°	508
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 527 cd/sqm

TEST NUMBER: P1282568

CATALOG NUMBER: P3AS09R15B2750DE010 E3CD1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	417.7	57.2
10°-20°	248.3	34.0
20°-30°	52.2	7.1
30°-40°	8.4	1.2
40°-50°	1.4	0.2
50°-60°	1.1	0.1
60°-70°	0.7	0.1
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	718.1	98.4
0°-40°	726.5	99.5
0°-60°	729.0	99.9
0°-90°	730.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	730.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6471	
5°	5403	418
15°	744	248
25°	100	52
35°	10	8
45°	2	1
55°	1	1
65°	1	1
75°	1	0
85°	0	0
90°	0	

TEST NUMBER: P1282568

CATALOG NUMBER: P3AS09R15B2750DE010 E3CD1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	6470.9
1°	6450.7
2°	6348.0
3°	6142.5
4°	5841.2
5°	5402.6
6°	4887.2
7°	4298.0
8°	3735.3
9°	3098.1
10°	2515.8
12.5°	1357.4
15°	743.9
17.5°	435.7
20°	267.8
22.5°	163.9
25°	100.4
27.5°	60.6
30°	35.8
32.5°	20.2
35°	10.4
37.5°	5.8
40°	3.5
42.5°	2.3
45°	1.7
47.5°	1.2
50°	1.2
52.5°	1.2
55°	1.2
57.5°	1.2
60°	1.2
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)