

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283533

Luminaire Tested: P3AS09R45B2750DE010 E3DLP1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283533
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R45B2750DE010 E3DLP1GPH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 3000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 204.0 lumens
Efficiency: N/A
Efficacy: 15.6 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283533

CATALOG NUMBER: P3AS09R45B2750DE010 E3DLP1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1283533

CATALOG NUMBER: P3AS09R45B2750DE010 E3DLP1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60763
5°	59388
10°	54775
15°	47628
20°	39133
25°	30437
30°	22484
35°	15821
40°	9876
45°	5334
50°	2900
55°	2485
60°	2237
65°	1920
70°	1603
75°	1694
80°	1389
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5334 cd/sqm

TEST NUMBER: P1283533

CATALOG NUMBER: P3AS09R45B2750DE010 E3DLP1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.0	12.2
10°-20°	58.0	28.4
20°-30°	57.6	28.2
30°-40°	37.1	18.2
40°-50°	14.3	7.0
50°-60°	5.8	2.9
60°-70°	3.7	1.8
70°-80°	2.0	1.0
80°-90°	0.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	140.6	68.9
0°-40°	177.7	87.1
0°-60°	197.8	96.9
0°-90°	204.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	204.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	277	
5°	270	25
15°	210	58
25°	126	58
35°	59	37
45°	17	14
55°	6	6
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1283533

CATALOG NUMBER: P3AS09R45B2750DE010 E3DLP1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	277.1
2.5°	275.7
5°	269.8
7.5°	259.6
10°	246.0
12.5°	229.0
15°	209.8
17.5°	188.9
20°	167.7
22.5°	146.2
25°	125.8
27.5°	106.6
30°	88.8
32.5°	73.2
35°	59.1
37.5°	46.4
40°	34.5
42.5°	24.9
45°	17.2
47.5°	11.6
50°	8.5
52.5°	7.1
55°	6.5
57.5°	5.7
60°	5.1
62.5°	4.2
65°	3.7
67.5°	3.1
70°	2.5
72.5°	2.3
75°	2.0
77.5°	1.4
80°	1.1
82.5°	0.8
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)