

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282683

Luminaire Tested: P3AS09R15B2750DE010 E3DLP1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282683
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R15B2750DE010 E3DLP1WMH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 355.0 lumens
Efficiency: N/A
Efficacy: 27.1 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282683

CATALOG NUMBER: P3AS09R15B2750DE010 E3DLP1WMH_3000K

Luminous Intensity Polar Plot



CATALOG NUMBER: P3AS09R15B2750DE010 E3DLP1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93		
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80		
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75		
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70		
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66		
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62		
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59		
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56		
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	153080
5°	141492
10°	112957
15°	85335
20°	64966
25°	49527
30°	35474
35°	23155
40°	14198
45°	8590
50°	5697
55°	4396
60°	3772
65°	3269
70°	2949
75°	2965
80°	2147
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Luminance: 8590 cd/sqm

TEST NUMBER: P1282683

CATALOG NUMBER: P3AS09R15B2750DE010 E3DLP1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.9	16.0
10°-20°	105.1	29.6
20°-30°	93.5	26.3
30°-40°	55.3	15.6
40°-50°	22.7	6.4
50°-60°	10.6	3.0
60°-70°	6.5	1.8
70°-80°	3.4	1.0
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	255.5	72.0
0°-40°	310.9	87.6
0°-60°	344.2	97.0
0°-90°	355.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	355.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	698	
5°	643	57
15°	376	105
25°	205	94
35°	86	55
45°	28	23
55°	12	11
65°	6	6
75°	4	3
85°	1	1
90°	0	

TEST NUMBER: P1282683

CATALOG NUMBER: P3AS09R15B2750DE010 E3DLP1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	698.1
1°	696.4
2°	691.2
3°	680.8
4°	663.5
5°	642.8
6°	620.3
7°	593.8
8°	566.1
9°	537.9
10°	507.3
12.5°	437.5
15°	375.9
17.5°	322.8
20°	278.4
22.5°	239.2
25°	204.7
27.5°	171.2
30°	140.1
32.5°	111.8
35°	86.5
37.5°	66.3
40°	49.6
42.5°	36.9
45°	27.7
47.5°	21.3
50°	16.7
52.5°	13.8
55°	11.5
57.5°	9.8
60°	8.6
62.5°	7.5
65°	6.3
67.5°	5.8
70°	4.6
72.5°	4.0
75°	3.5
77.5°	2.3
80°	1.7
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)