

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283560

Luminaire Tested: P3AS09R45B2750DE010 E3DLP1WMH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283560
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R45B2750DE010 E3DLP1WMH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 4000K CCT AND, 80CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 423.0 lumens
Efficiency: N/A
Efficacy: 32.3 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283560

CATALOG NUMBER: P3AS09R45B2750DE010 E3DLP1WMH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1283560

CATALOG NUMBER: P3AS09R45B2750DE010 E3DLP1WMH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97	96	94		93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87		86
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86	83	81		79
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81	78	75		74
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77	73	70		69
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73	69	66		64
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		69	65	61		60
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65	61	58		56
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62	58	55		53
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59	55	52		50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125999
5°	123112
10°	113581
15°	98752
20°	81137
25°	63125
30°	46615
35°	32792
40°	20467
45°	11102
50°	6004
55°	5161
60°	4649
65°	3943
70°	3398
75°	3474
80°	2904
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11102 cd/sqm

TEST NUMBER: P1283560

CATALOG NUMBER: P3AS09R45B2750DE010 E3DLP1WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.8	12.2
10°-20°	120.3	28.4
20°-30°	119.4	28.2
30°-40°	76.9	18.2
40°-50°	29.6	7.0
50°-60°	12.1	2.8
60°-70°	7.6	1.8
70°-80°	4.1	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	291.5	68.9
0°-40°	368.4	87.1
0°-60°	410.0	96.9
0°-90°	423.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	423.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	575	
5°	559	52
15°	435	120
25°	261	119
35°	122	77
45°	36	30
55°	14	12
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1283560

CATALOG NUMBER: P3AS09R45B2750DE010 E3DLP1WMH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	574.6
2.5°	571.7
5°	559.3
7.5°	538.2
10°	510.1
12.5°	474.9
15°	435.0
17.5°	391.7
20°	347.7
22.5°	303.1
25°	260.9
27.5°	221.0
30°	184.1
32.5°	151.9
35°	122.5
37.5°	96.2
40°	71.5
42.5°	51.6
45°	35.8
47.5°	24.0
50°	17.6
52.5°	14.7
55°	13.5
57.5°	11.7
60°	10.6
62.5°	8.8
65°	7.6
67.5°	6.4
70°	5.3
72.5°	4.7
75°	4.1
77.5°	2.9
80°	2.3
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)