

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283588

Luminaire Tested: P3AS09R50B2750DE010 E3CD1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283588
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R50B2750DE010 E3CD1MW_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3CD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 790.0 lumens
Efficiency: N/A
Efficacy: 60.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283588

CATALOG NUMBER: P3AS09R50B2750DE010 E3CD1MW_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1283588

CATALOG NUMBER: P3AS09R50B2750DE010 E3CD1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	114	112	109	107	112	109	107	106	105	104	102		102	101	99		98	97	96		95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	93	91		90
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91	88	86		85
4	100	94	89	85	99	92	88	85	90	87	84		88	85	83		87	84	82		80
5	96	89	84	80	94	88	83	79	86	82	79		84	81	78		83	80	77		76
6	92	84	79	75	91	83	79	75	82	78	74		81	77	74		79	76	73		72
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76	73	70		69
8	85	76	71	67	83	76	71	67	75	70	67		74	70	67		73	69	66		65
9	81	73	68	64	80	72	67	64	71	67	64		71	66	63		70	66	63		62
10	78	69	64	61	77	69	64	61	68	64	61		68	63	61		67	63	60		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	275131
5°	270217
10°	259447
15°	237913
20°	209785
25°	160800
30°	87431
35°	28134
40°	6612
45°	899
50°	785
55°	879
60°	746
65°	882
70°	769
75°	1017
80°	758
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 85°

Luminance: 1510 cd/sqm

TEST NUMBER: P1283588

CATALOG NUMBER: P3AS09R50B2750DE010 E3CD1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.2	14.6
10°-20°	291.3	36.9
20°-30°	291.7	36.9
30°-40°	82.0	10.4
40°-50°	5.0	0.6
50°-60°	1.9	0.2
60°-70°	1.5	0.2
70°-80°	1.0	0.1
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	698.3	88.4
0°-40°	780.3	98.8
0°-60°	787.1	99.6
0°-90°	790.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	790.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1255	
5°	1228	115
15°	1048	291
25°	665	292
35°	105	82
45°	3	5
55°	2	2
65°	2	1
75°	1	1
85°	1	0
90°	0	

TEST NUMBER: P1283588

CATALOG NUMBER: P3AS09R50B2750DE010 E3CD1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1254.7
2.5°	1248.4
5°	1227.6
7.5°	1199.3
10°	1165.2
12.5°	1113.8
15°	1048.0
17.5°	972.4
20°	899.0
22.5°	807.8
25°	664.6
27.5°	494.8
30°	345.3
32.5°	208.4
35°	105.1
37.5°	49.7
40°	23.1
42.5°	8.7
45°	2.9
47.5°	2.3
50°	2.3
52.5°	2.3
55°	2.3
57.5°	1.7
60°	1.7
62.5°	1.7
65°	1.7
67.5°	1.2
70°	1.2
72.5°	1.2
75°	1.2
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0

(END OF REPORT)