

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283608

Luminaire Tested: P3AS09R50B2750DE010 E3D1WH_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283608
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R50B2750DE010 E3D1WH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 801.0 lumens
Efficiency: N/A
Efficacy: 61.1 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283608

CATALOG NUMBER: P3AS09R50B2750DE010 E3D1WH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1283608

CATALOG NUMBER: P3AS09R50B2750DE010 E3D1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	109	107		112	110	108	106		105	104	102		102	101	99		98	97	97
2	109	105	101	98		107	103	100	97		100	97	95		97	95	93		94	93	91
3	105	99	95	91		103	98	94	90		95	92	89		93	90	88		91	88	86
4	100	94	89	85		99	92	88	85		90	87	84		88	85	83		87	84	82
5	96	89	84	80		94	88	83	79		86	82	79		84	81	78		83	80	77
6	92	84	79	75		91	83	78	75		82	78	74		81	77	74		79	76	73
7	88	80	75	71		87	79	74	71		78	74	70		77	73	70		76	72	70
8	84	76	71	67		83	76	71	67		75	70	67		74	69	66		73	69	66
9	81	73	67	64		80	72	67	64		71	67	63		70	66	63		70	66	63
10	78	69	64	61		77	69	64	61		68	64	60		67	63	60		67	63	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	279912
5°	272462
10°	260004
15°	235393
20°	203648
25°	167042
30°	95964
35°	29794
40°	8015
45°	2791
50°	682
55°	229
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2791 cd/sqm

TEST NUMBER: P1283608

CATALOG NUMBER: P3AS09R50B2750DE010 E3D1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.9	14.5
10°-20°	287.3	35.9
20°-30°	302.0	37.7
30°-40°	86.4	10.8
40°-50°	8.4	1.1
50°-60°	0.7	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	705.2	88.0
0°-40°	791.6	98.8
0°-60°	800.8	100.0
0°-90°	801.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	801.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1276	
5°	1238	116
15°	1037	287
25°	690	302
35°	111	86
45°	9	8
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1283608

CATALOG NUMBER: P3AS09R50B2750DE010 E3D1WH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1276.5
1°	1274.5
2°	1268.9
3°	1260.7
4°	1249.7
5°	1237.8
6°	1225.1
7°	1211.5
8°	1198.8
9°	1184.1
10°	1167.7
11°	1148.8
12°	1127.0
13°	1099.9
14°	1070.5
15°	1036.9
16°	1001.3
17°	966.8
18°	931.5
19°	900.4
20°	872.7
21°	846.1
22°	815.9
23°	781.1
24°	740.4
25°	690.4
26°	636.1
27°	575.7
28°	515.5
29°	450.5
30°	379.0
31°	312.0
32°	250.4
32.5°	223.5
33°	196.4
34°	150.6
35°	111.3
36°	81.7
37°	60.8
37.5°	52.6
38°	45.5
39°	35.3
40°	28.0
42.5°	15.8
45°	9.0



TEST NUMBER: P1283608

CATALOG NUMBER: P3AS09R50B2750DE010 E3D1WH_3000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	5.1
50°	2.0
52.5°	0.8
55°	0.6
57.5°	0.6
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)