

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283647

Luminaire Tested: P3AS09R50B2750DE010 E3DLD1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283647
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R50B2750DE010 E3DLD1GPH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 2700K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 251.0 lumens
Efficiency: N/A
Efficacy: 19.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283647

CATALOG NUMBER: P3AS09R50B2750DE010 E3DLD1GPH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1283647

CATALOG NUMBER: P3AS09R50B2750DE010 E3DLD1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95	94	93		91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	86	84		83
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83	80	77		75
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77	73	70		69
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72	68	64		63
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67	63	59		58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55		53
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59	55	51		50
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56	51	48		46
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53	48	45		43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51005
5°	50253
10°	48029
15°	44472
20°	39973
25°	35131
30°	29878
35°	24226
40°	18206
45°	11722
50°	5561
55°	4396
60°	4166
65°	3840
70°	3462
75°	3135
80°	2904
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11722 cd/sqm

TEST NUMBER: P1283647

CATALOG NUMBER: P3AS09R50B2750DE010 E3DLD1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.4	8.5
10°-20°	54.6	21.8
20°-30°	66.4	26.4
30°-40°	56.3	22.4
40°-50°	29.2	11.6
50°-60°	10.6	4.2
60°-70°	7.3	2.9
70°-80°	4.0	1.6
80°-90°	1.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	142.4	56.7
0°-40°	198.7	79.2
0°-60°	238.5	95.0
0°-90°	251.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	251.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	233	
5°	228	21
15°	196	55
25°	145	66
35°	90	56
45°	38	29
55°	12	11
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1283647

CATALOG NUMBER: P3AS09R50B2750DE010 E3DLD1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	232.6
2.5°	231.8
5°	228.3
7.5°	223.2
10°	215.7
12.5°	206.3
15°	195.9
17.5°	184.2
20°	171.3
22.5°	158.1
25°	145.2
27.5°	131.8
30°	118.0
32.5°	104.3
35°	90.5
37.5°	77.1
40°	63.6
42.5°	50.7
45°	37.8
47.5°	25.2
50°	16.3
52.5°	12.6
55°	11.5
57.5°	10.3
60°	9.5
62.5°	8.3
65°	7.4
67.5°	6.3
70°	5.4
72.5°	4.6
75°	3.7
77.5°	2.9
80°	2.3
82.5°	1.7
85°	1.1
87.5°	0.6
90°	0.0

(END OF REPORT)