

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283662

Luminaire Tested: P3AS09R50B2750DE010 E3DLD1MW\_2700K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1283662  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R50B2750DE010 E3DLD1MW\_2700K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 2700K CCT AND, 90CRI , E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 513.0 lumens  
Efficiency: N/A  
Efficacy: 39.2 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1283662

CATALOG NUMBER: P3AS09R50B2750DE010 E3DLD1MW\_2700K

### Luminous Intensity Polar Plot



TEST NUMBER: P1283662

CATALOG NUMBER: P3AS09R50B2750DE010 E3DLD1MW\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 102 | 103 | 101 | 99  |  | 99  | 97  | 96  |  | 95  |
| 2   | 106 | 100 | 95  | 91  | 103 | 98  | 94  | 90  | 95  | 91  | 88  |  | 92  | 89  | 86  |  | 89  |
| 3   | 99  | 92  | 86  | 81  | 97  | 90  | 85  | 81  | 88  | 83  | 79  |  | 85  | 81  | 78  |  | 83  |
| 4   | 93  | 85  | 78  | 73  | 91  | 83  | 77  | 73  | 81  | 76  | 72  |  | 79  | 75  | 71  |  | 77  |
| 5   | 88  | 78  | 72  | 67  | 86  | 77  | 71  | 66  | 75  | 70  | 66  |  | 74  | 69  | 65  |  | 72  |
| 6   | 83  | 73  | 66  | 61  | 81  | 72  | 65  | 61  | 70  | 65  | 60  |  | 69  | 64  | 60  |  | 67  |
| 7   | 78  | 68  | 61  | 56  | 77  | 67  | 61  | 56  | 66  | 60  | 56  |  | 64  | 59  | 55  |  | 63  |
| 8   | 74  | 63  | 57  | 52  | 73  | 63  | 56  | 52  | 61  | 56  | 52  |  | 60  | 55  | 51  |  | 59  |
| 9   | 70  | 59  | 53  | 48  | 69  | 59  | 52  | 48  | 58  | 52  | 48  |  | 57  | 52  | 48  |  | 56  |
| 10  | 66  | 56  | 49  | 45  | 65  | 55  | 49  | 45  | 54  | 49  | 45  |  | 54  | 48  | 45  |  | 53  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 104246 |
| 5°  | 102707 |
| 10° | 98172  |
| 15° | 90920  |
| 20° | 81697  |
| 25° | 71811  |
| 30° | 61073  |
| 35° | 49523  |
| 40° | 37213  |
| 45° | 23971  |
| 50° | 11394  |
| 55° | 8946   |
| 60° | 8464   |
| 65° | 7887   |
| 70° | 7117   |
| 75° | 6439   |
| 80° | 5935   |
| 85° | 5787   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23971 cd/sqm

TEST NUMBER: P1283662

CATALOG NUMBER: P3AS09R50B2750DE010 E3DLD1MW\_2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 43.7   | 8.5       |
| 10°-20°   | 111.7  | 21.8      |
| 20°-30°   | 135.6  | 26.4      |
| 30°-40°   | 115.0  | 22.4      |
| 40°-50°   | 59.8   | 11.6      |
| 50°-60°   | 21.6   | 4.2       |
| 60°-70°   | 14.9   | 2.9       |
| 70°-80°   | 8.1    | 1.6       |
| 80°-90°   | 2.5    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 291.1  | 56.7      |
| 0°-40°    | 406.1  | 79.2      |
| 0°-60°    | 487.4  | 95.0      |
| 0°-90°    | 513.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 513.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 475 |      |
| 5°  | 467 | 44   |
| 15° | 400 | 112  |
| 25° | 297 | 136  |
| 35° | 185 | 115  |
| 45° | 77  | 60   |
| 55° | 23  | 22   |
| 65° | 15  | 15   |
| 75° | 8   | 8    |
| 85° | 2   | 3    |
| 90° | 0   |      |

TEST NUMBER: P1283662

CATALOG NUMBER: P3AS09R50B2750DE010 E3DLD1MW\_2700K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 475.4 |
| 2.5°  | 473.7 |
| 5°    | 466.6 |
| 7.5°  | 456.1 |
| 10°   | 440.9 |
| 12.5° | 421.6 |
| 15°   | 400.5 |
| 17.5° | 376.5 |
| 20°   | 350.1 |
| 22.5° | 323.2 |
| 25°   | 296.8 |
| 27.5° | 269.3 |
| 30°   | 241.2 |
| 32.5° | 213.1 |
| 35°   | 185.0 |
| 37.5° | 157.5 |
| 40°   | 130.0 |
| 42.5° | 103.6 |
| 45°   | 77.3  |
| 47.5° | 51.5  |
| 50°   | 33.4  |
| 52.5° | 25.8  |
| 55°   | 23.4  |
| 57.5° | 21.1  |
| 60°   | 19.3  |
| 62.5° | 17.0  |
| 65°   | 15.2  |
| 67.5° | 12.9  |
| 70°   | 11.1  |
| 72.5° | 9.4   |
| 75°   | 7.6   |
| 77.5° | 5.9   |
| 80°   | 4.7   |
| 82.5° | 3.5   |
| 85°   | 2.3   |
| 87.5° | 1.2   |
| 90°   | 0.0   |

(END OF REPORT)