

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283673

Luminaire Tested: P3AS09R50B2750DE010 E3DLD1WMH\_3000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1283673  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R50B2750DE010 E3DLD1WMH\_3000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 505.1 lumens  
Efficiency: N/A  
Efficacy: 38.6 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1283673

CATALOG NUMBER: P3AS09R50B2750DE010 E3DLD1WMH\_3000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1283673

CATALOG NUMBER: P3AS09R50B2750DE010 E3DLD1WMH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    | 20 |    |    |    | 20 |    |    |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    |    | 0  |    |    |    | 0  |    |    |    | 0  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |    |    |    |    |    |    |    |    |    |
| 1   | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 102 | 103 | 101 | 99  | 99  | 97  | 96  | 95  | 94  | 93  | 91  |    |    |    |    |    |    |    |    |    |    |    |
| 2   | 106 | 100 | 95  | 91  | 103 | 98  | 94  | 90  | 95  | 91  | 88  | 92  | 89  | 86  | 89  | 86  | 84  | 83  |    |    |    |    |    |    |    |    |    |    |    |
| 3   | 99  | 92  | 86  | 81  | 97  | 90  | 85  | 81  | 88  | 83  | 79  | 85  | 81  | 78  | 83  | 80  | 77  | 75  |    |    |    |    |    |    |    |    |    |    |    |
| 4   | 93  | 85  | 78  | 73  | 91  | 83  | 77  | 73  | 81  | 76  | 72  | 79  | 75  | 71  | 77  | 73  | 70  | 69  |    |    |    |    |    |    |    |    |    |    |    |
| 5   | 88  | 78  | 72  | 67  | 86  | 77  | 71  | 66  | 75  | 70  | 66  | 74  | 69  | 65  | 72  | 68  | 64  | 63  |    |    |    |    |    |    |    |    |    |    |    |
| 6   | 83  | 73  | 66  | 61  | 81  | 72  | 65  | 61  | 70  | 65  | 60  | 69  | 64  | 60  | 67  | 63  | 59  | 58  |    |    |    |    |    |    |    |    |    |    |    |
| 7   | 78  | 68  | 61  | 56  | 77  | 67  | 61  | 56  | 66  | 60  | 56  | 64  | 59  | 55  | 63  | 59  | 55  | 53  |    |    |    |    |    |    |    |    |    |    |    |
| 8   | 74  | 63  | 57  | 52  | 73  | 63  | 56  | 52  | 61  | 56  | 52  | 60  | 55  | 51  | 59  | 55  | 51  | 50  |    |    |    |    |    |    |    |    |    |    |    |
| 9   | 70  | 59  | 53  | 48  | 69  | 59  | 52  | 48  | 58  | 52  | 48  | 57  | 52  | 48  | 56  | 51  | 48  | 46  |    |    |    |    |    |    |    |    |    |    |    |
| 10  | 66  | 56  | 49  | 45  | 65  | 55  | 49  | 45  | 54  | 49  | 45  | 54  | 48  | 45  | 53  | 48  | 45  | 43  |    |    |    |    |    |    |    |    |    |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 102623 |
| 5°  | 101122 |
| 10° | 96636  |
| 15° | 89490  |
| 20° | 80437  |
| 25° | 70698  |
| 30° | 60136  |
| 35° | 48747  |
| 40° | 36640  |
| 45° | 23599  |
| 50° | 11224  |
| 55° | 8831   |
| 60° | 8333   |
| 65° | 7783   |
| 70° | 7052   |
| 75° | 6354   |
| 80° | 5809   |
| 85° | 5787   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23599 cd/sqm

TEST NUMBER: P1283673

CATALOG NUMBER: P3AS09R50B2750DE010 E3DLD1WMH\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 43.1   | 8.5       |
| 10°-20°   | 109.9  | 21.8      |
| 20°-30°   | 133.5  | 26.4      |
| 30°-40°   | 113.3  | 22.4      |
| 40°-50°   | 58.8   | 11.6      |
| 50°-60°   | 21.2   | 4.2       |
| 60°-70°   | 14.7   | 2.9       |
| 70°-80°   | 8.0    | 1.6       |
| 80°-90°   | 2.5    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 286.5  | 56.7      |
| 0°-40°    | 399.8  | 79.2      |
| 0°-60°    | 479.8  | 95.0      |
| 0°-90°    | 505.1  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 505.1  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 468 |      |
| 5°  | 459 | 43   |
| 15° | 394 | 110  |
| 25° | 292 | 134  |
| 35° | 182 | 113  |
| 45° | 76  | 59   |
| 55° | 23  | 21   |
| 65° | 15  | 15   |
| 75° | 8   | 8    |
| 85° | 2   | 3    |
| 90° | 0   |      |

TEST NUMBER: P1283673

CATALOG NUMBER: P3AS09R50B2750DE010 E3DLD1WMH\_3000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 468.0 |
| 2.5°  | 466.3 |
| 5°    | 459.4 |
| 7.5°  | 449.0 |
| 10°   | 434.0 |
| 12.5° | 415.0 |
| 15°   | 394.2 |
| 17.5° | 370.6 |
| 20°   | 344.7 |
| 22.5° | 318.2 |
| 25°   | 292.2 |
| 27.5° | 265.1 |
| 30°   | 237.5 |
| 32.5° | 209.8 |
| 35°   | 182.1 |
| 37.5° | 155.0 |
| 40°   | 128.0 |
| 42.5° | 102.0 |
| 45°   | 76.1  |
| 47.5° | 50.7  |
| 50°   | 32.9  |
| 52.5° | 25.4  |
| 55°   | 23.1  |
| 57.5° | 20.7  |
| 60°   | 19.0  |
| 62.5° | 16.7  |
| 65°   | 15.0  |
| 67.5° | 12.7  |
| 70°   | 11.0  |
| 72.5° | 9.2   |
| 75°   | 7.5   |
| 77.5° | 5.8   |
| 80°   | 4.6   |
| 82.5° | 3.5   |
| 85°   | 2.3   |
| 87.5° | 1.2   |
| 90°   | 0.0   |

(END OF REPORT)