

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282867

Luminaire Tested: P3AS09R25B2750DE010 E3D1LI\_2700K

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1282867  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R25B2750DE010 E3D1LI\_2700K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI , E3D1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 791.0 lumens  
Efficiency: N/A  
Efficacy: 60.4 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1282867

CATALOG NUMBER: P3AS09R25B2750DE010 E3D1LI\_2700K

### Luminous Intensity Polar Plot



TEST NUMBER: P1282867

CATALOG NUMBER: P3AS09R25B2750DE010 E3D1LI\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 0  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 99 | 99 |
| 1   | 115 | 113 | 111 | 110 | 113 | 111 | 110 | 108 | 107 | 106 | 105 | 104 | 103 | 102 | 100 | 99  | 99  | 97  | 96 | 96 |
| 2   | 112 | 108 | 106 | 103 | 110 | 107 | 104 | 102 | 104 | 102 | 100 | 101 | 99  | 98  | 98  | 97  | 96  | 94  | 93 | 93 |
| 3   | 109 | 104 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 98  | 96  | 98  | 96  | 94  | 96  | 94  | 93  | 92  | 91 | 91 |
| 4   | 106 | 101 | 97  | 94  | 104 | 100 | 96  | 94  | 98  | 95  | 92  | 96  | 93  | 91  | 94  | 92  | 90  | 89  | 88 | 88 |
| 5   | 103 | 97  | 93  | 91  | 101 | 96  | 93  | 90  | 95  | 92  | 90  | 93  | 91  | 89  | 92  | 90  | 88  | 87  | 86 | 86 |
| 6   | 100 | 94  | 90  | 88  | 99  | 94  | 90  | 87  | 92  | 89  | 87  | 91  | 88  | 86  | 90  | 88  | 86  | 85  | 84 | 84 |
| 7   | 98  | 92  | 88  | 85  | 97  | 91  | 87  | 85  | 90  | 87  | 84  | 89  | 86  | 84  | 88  | 86  | 84  | 83  | 82 | 82 |
| 8   | 95  | 89  | 85  | 83  | 94  | 89  | 85  | 83  | 88  | 85  | 82  | 87  | 84  | 82  | 86  | 84  | 82  | 81  | 80 | 80 |
| 9   | 93  | 87  | 83  | 81  | 92  | 86  | 83  | 80  | 86  | 83  | 80  | 85  | 82  | 80  | 84  | 82  | 80  | 79  | 78 | 78 |
| 10  | 91  | 85  | 81  | 79  | 90  | 84  | 81  | 79  | 84  | 81  | 78  | 83  | 80  | 78  | 83  | 80  | 78  | 77  | 76 | 76 |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 866290 |
| 5°  | 802485 |
| 10° | 620897 |
| 15° | 296574 |
| 20° | 97775  |
| 25° | 41228  |
| 30° | 15977  |
| 35° | 6906   |
| 40° | 2290   |
| 45° | 1054   |
| 50° | 375    |
| 55° | 229    |
| 60° | 132    |
| 65° | 156    |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 1054 cd/sqm

TEST NUMBER: P1282867

CATALOG NUMBER: P3AS09R25B2750DE010 E3D1LI\_2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 320.5  | 40.5      |
| 10°-20°   | 364.5  | 46.1      |
| 20°-30°   | 84.7   | 10.7      |
| 30°-40°   | 17.8   | 2.2       |
| 40°-50°   | 2.9    | 0.4       |
| 50°-60°   | 0.5    | 0.1       |
| 60°-70°   | 0.3    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 769.6  | 97.3      |
| 0°-40°    | 787.4  | 99.5      |
| 0°-60°    | 790.8  | 100.0     |
| 0°-90°    | 791.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 791.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3951 |      |
| 5°  | 3646 | 320  |
| 15° | 1306 | 364  |
| 25° | 170  | 85   |
| 35° | 26   | 18   |
| 45° | 3    | 3    |
| 55° | 1    | 0    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1282867

CATALOG NUMBER: P3AS09R25B2750DE010 E3D1LI\_2700K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 3950.6 |
| 1°    | 3942.6 |
| 2°    | 3901.6 |
| 3°    | 3843.9 |
| 4°    | 3755.9 |
| 5°    | 3645.7 |
| 6°    | 3504.4 |
| 7°    | 3356.4 |
| 8°    | 3190.3 |
| 9°    | 3003.0 |
| 10°   | 2788.5 |
| 11°   | 2539.9 |
| 12°   | 2254.5 |
| 13°   | 1941.9 |
| 14°   | 1614.9 |
| 15°   | 1306.4 |
| 16°   | 1033.3 |
| 17°   | 805.0  |
| 18°   | 633.2  |
| 19°   | 506.5  |
| 20°   | 419.0  |
| 21°   | 350.2  |
| 22°   | 294.0  |
| 23°   | 245.5  |
| 24°   | 205.3  |
| 25°   | 170.4  |
| 27.5° | 101.0  |
| 30°   | 63.1   |
| 32.5° | 40.4   |
| 35°   | 25.8   |
| 37.5° | 15.5   |
| 40°   | 8.0    |
| 42.5° | 5.2    |
| 45°   | 3.4    |
| 47.5° | 2.0    |
| 50°   | 1.1    |
| 52.5° | 0.6    |
| 55°   | 0.6    |
| 57.5° | 0.3    |
| 60°   | 0.3    |
| 62.5° | 0.3    |
| 65°   | 0.3    |
| 67.5° | 0.3    |
| 70°   | 0.0    |
| 72.5° | 0.0    |



TEST NUMBER: P1282867

CATALOG NUMBER: P3AS09R25B2750DE010 E3D1LI\_2700K

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

(END OF REPORT)