

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283678

Luminaire Tested: P3AS09R50B2750DE010 E3DLP1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283678
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R50B2750DE010 E3DLP1GPH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 209.0 lumens
Efficiency: N/A
Efficacy: 16.0 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283678

CATALOG NUMBER: P3AS09R50B2750DE010 E3DLP1GPH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1283678

CATALOG NUMBER: P3AS09R50B2750DE010 E3DLP1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97	95	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86	83	81	79
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81	78	75	73
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		77	73	70	68
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72	68	65	64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68	64	61	60
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65	61	57	56
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62	57	54	53
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59	54	51	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60785
5°	59146
10°	54553
15°	47968
20°	40137
25°	31816
30°	23345
35°	16062
40°	10191
45°	5706
50°	3104
55°	2600
60°	2237
65°	2075
70°	1795
75°	1694
80°	1389
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5706 cd/sqm

TEST NUMBER: P1283678

CATALOG NUMBER: P3AS09R50B2750DE010 E3DLP1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.9	11.9
10°-20°	58.5	28.0
20°-30°	59.9	28.6
30°-40°	38.0	18.2
40°-50°	15.1	7.2
50°-60°	6.1	2.9
60°-70°	3.9	1.9
70°-80°	2.0	1.0
80°-90°	0.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	143.3	68.6
0°-40°	181.2	86.7
0°-60°	202.4	96.9
0°-90°	209.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	209.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	277	
5°	269	25
15°	211	59
25°	132	60
35°	60	38
45°	18	15
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1283678

CATALOG NUMBER: P3AS09R50B2750DE010 E3DLP1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	277.2
2.5°	275.2
5°	268.7
7.5°	258.5
10°	245.0
12.5°	228.8
15°	211.3
17.5°	192.1
20°	172.0
22.5°	151.9
25°	131.5
27.5°	111.2
30°	92.2
32.5°	75.2
35°	60.0
37.5°	47.0
40°	35.6
42.5°	26.3
45°	18.4
47.5°	12.4
50°	9.1
52.5°	7.6
55°	6.8
57.5°	5.9
60°	5.1
62.5°	4.5
65°	4.0
67.5°	3.4
70°	2.8
72.5°	2.3
75°	2.0
77.5°	1.4
80°	1.1
82.5°	0.8
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)