

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282891

Luminaire Tested: P3AS09R25B2750DE010 E3DL1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282891
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R25B2750DE010 E3DL1GPH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 80CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 321.0 lumens
Efficiency: N/A
Efficacy: 24.5 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282891

CATALOG NUMBER: P3AS09R25B2750DE010 E3DL1GPH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1282891

CATALOG NUMBER: P3AS09R25B2750DE010 E3DL1GPH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97		95
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95	93	92		90
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91	89	87		86
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88	85	83		82
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85	82	79		78
6	94	86	81	78	92	86	81	78	84	80	77		83	79	77		82	78	76		75
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79	75	73		72
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76	73	70		69
9	84	76	71	68	83	76	71	68	75	71	68		74	70	68		73	70	67		66
10	81	73	69	65	80	73	68	65	72	68	65		72	68	65		71	67	65		64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	205905
5°	192119
10°	153905
15°	104473
20°	63215
25°	36970
30°	21041
35°	11591
40°	6154
45°	3225
50°	1876
55°	1415
60°	1228
65°	1297
70°	1154
75°	1017
80°	758
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3225 cd/sqm

TEST NUMBER: P1282891

CATALOG NUMBER: P3AS09R25B2750DE010 E3DL1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.4	24.1
10°-20°	126.5	39.4
20°-30°	72.3	22.5
30°-40°	28.5	8.9
40°-50°	8.7	2.7
50°-60°	3.5	1.1
60°-70°	2.3	0.7
70°-80°	1.3	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	276.3	86.1
0°-40°	304.8	95.0
0°-60°	317.0	98.8
0°-90°	321.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	321.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	939	
5°	873	77
15°	460	127
25°	153	72
35°	43	29
45°	10	9
55°	4	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1282891

CATALOG NUMBER: P3AS09R25B2750DE010 E3DL1GPH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	939.0
1°	937.2
2°	929.5
3°	916.0
4°	897.3
5°	872.8
6°	843.9
7°	811.4
8°	773.7
9°	735.0
10°	691.2
11°	647.9
12°	600.3
13°	553.4
14°	505.2
15°	460.2
17.5°	356.8
20°	270.9
22.5°	203.4
25°	152.8
27.5°	113.2
30°	83.1
32.5°	60.1
35°	43.3
37.5°	30.7
40°	21.5
42.5°	14.7
45°	10.4
47.5°	7.4
50°	5.5
52.5°	4.3
55°	3.7
57.5°	3.4
60°	2.8
62.5°	2.5
65°	2.5
67.5°	2.1
70°	1.8
72.5°	1.5
75°	1.2
77.5°	0.9
80°	0.6
82.5°	0.6
85°	0.3
87.5°	0.3



TEST NUMBER: P1282891

CATALOG NUMBER: P3AS09R25B2750DE010 E3DL1GPH_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)