

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283701

Luminaire Tested: P3AS09R50B2750DE010 E3DLP1WH\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1283701  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R50B2750DE010 E3DLP1WH\_5000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 5000K CCT AND, 80CRI , E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 705.0 lumens  
Efficiency: N/A  
Efficacy: 53.8 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 13.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1283701  
CATALOG NUMBER: P3AS09R50B2750DE010 E3DLP1WH\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1283701

CATALOG NUMBER: P3AS09R50B2750DE010 E3DLP1WH\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94				94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87				87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82				82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76				76
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72				72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67				67
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64				64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60				60
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57				57
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54				54

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	224456
5°	219942
10°	206008
15°	184428
20°	155203
25°	118458
30°	76974
35°	45642
40°	26364
45°	13211
50°	4912
55°	3823
60°	3552
65°	3269
70°	3206
75°	3219
80°	3157
85°	3271

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13211 cd/sqm



TEST NUMBER: P1283701

CATALOG NUMBER: P3AS09R50B2750DE010 E3DLP1WH\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.0	13.2
10°-20°	224.7	31.9
20°-30°	220.4	31.3
30°-40°	111.0	15.8
40°-50°	35.1	5.0
50°-60°	9.1	1.3
60°-70°	6.4	0.9
70°-80°	4.0	0.6
80°-90°	1.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	538.0	76.3
0°-40°	649.1	92.1
0°-60°	693.2	98.3
0°-90°	705.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	705.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1024	
5°	999	93
15°	812	225
25°	490	220
35°	170	111
45°	43	35
55°	10	9
65°	6	6
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1283701  
CATALOG NUMBER: P3AS09R50B2750DE010 E3DLP1WH\_5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1023.6
2.5°	1017.3
5°	999.2
7.5°	966.6
10°	925.2
12.5°	871.9
15°	812.4
17.5°	743.4
20°	665.1
22.5°	580.4
25°	489.6
27.5°	393.0
30°	304.0
32.5°	228.8
35°	170.5
37.5°	126.0
40°	92.1
42.5°	65.2
45°	42.6
47.5°	24.4
50°	14.4
52.5°	10.7
55°	10.0
57.5°	8.8
60°	8.1
62.5°	7.5
65°	6.3
67.5°	5.6
70°	5.0
72.5°	4.4
75°	3.8
77.5°	3.1
80°	2.5
82.5°	1.9
85°	1.3
87.5°	0.6
90°	0.0

(END OF REPORT)