

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282967

Luminaire Tested: P3AS09R25B2750DE010 E3DLP1WH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282967
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R25B2750DE010 E3DLP1WH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 613.0 lumens
Efficiency: N/A
Efficacy: 46.8 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282967

CATALOG NUMBER: P3AS09R25B2750DE010 E3DLP1WH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1282967

CATALOG NUMBER: P3AS09R25B2750DE010 E3DLP1WH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	95	94	93	92	90	88	85	82
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	94	93	92	90	88	85	82	79	76	73	70
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	88	85	82	79	76	73	70	67	64	61	58
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	84	81	78	75	72	69	66	63	60	57	54
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	80	77	74	71	68	65	62	59	56	53	50
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	76	73	70	67	64	61	58	55	52	49	46
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	73	70	67	64	61	58	55	52	49	46	43
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	70	67	64	61	58	55	52	49	46	43	40
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	67	64	61	58	55	52	49	46	43	40	37
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	64	61	58	55	52	49	46	43	40	37	34
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	62	59	56	53	50	47	44	41	38	35	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	393214
5°	366871
10°	293893
15°	199479
20°	120714
25°	70577
30°	40209
35°	22111
40°	11736
45°	6171
50°	3582
55°	2676
60°	2324
65°	2439
70°	2244
75°	1949
80°	1515
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6171 cd/sqm

TEST NUMBER: P1282967

CATALOG NUMBER: P3AS09R25B2750DE010 E3DLP1WH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.9	24.1
10°-20°	241.6	39.4
20°-30°	138.1	22.5
30°-40°	54.5	8.9
40°-50°	16.7	2.7
50°-60°	6.6	1.1
60°-70°	4.4	0.7
70°-80°	2.5	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	527.5	86.1
0°-40°	582.0	94.9
0°-60°	605.3	98.7
0°-90°	613.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	613.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1793	
5°	1667	148
15°	879	242
25°	292	138
35°	83	54
45°	20	17
55°	7	7
65°	5	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1282967

CATALOG NUMBER: P3AS09R25B2750DE010 E3DLP1WH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1793.2
1°	1789.7
2°	1775.1
3°	1749.3
4°	1713.5
5°	1666.7
6°	1611.6
7°	1549.5
8°	1477.5
9°	1403.6
10°	1319.9
11°	1237.3
12°	1146.5
13°	1056.8
14°	964.9
15°	878.7
17.5°	681.3
20°	517.3
22.5°	388.4
25°	291.7
27.5°	216.2
30°	158.8
32.5°	114.8
35°	82.6
37.5°	58.6
40°	41.0
42.5°	28.1
45°	19.9
47.5°	14.1
50°	10.5
52.5°	8.2
55°	7.0
57.5°	6.4
60°	5.3
62.5°	4.7
65°	4.7
67.5°	4.1
70°	3.5
72.5°	2.9
75°	2.3
77.5°	1.8
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.6



TEST NUMBER: P1282967

CATALOG NUMBER: P3AS09R25B2750DE010 E3DLP1WH_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)