

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282976

Luminaire Tested: P3AS09R25B2750DE010 E3DLP1WMH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282976
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R25B2750DE010 E3DLP1WMH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 80CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 402.0 lumens
Efficiency: N/A
Efficacy: 30.7 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282976

CATALOG NUMBER: P3AS09R25B2750DE010 E3DLP1WMH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1282976

CATALOG NUMBER: P3AS09R25B2750DE010 E3DLP1WMH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	105		111	108	106	104		104	102	101		100	99	98		97	96	95
2	107	102	98	95		105	101	97	94		97	94	92		94	92	90		92	90	88
3	102	95	90	86		100	94	89	86		91	87	84		89	86	83		87	84	82
4	97	89	84	79		95	88	83	79		86	81	78		84	80	77		82	79	76
5	92	84	78	74		91	83	77	73		81	76	73		79	75	72		78	74	71
6	88	79	73	69		86	78	72	68		77	72	68		75	71	67		74	70	67
7	84	74	68	64		82	74	68	64		72	67	64		71	67	63		70	66	63
8	80	70	65	60		79	70	64	60		69	64	60		68	63	60		67	63	60
9	76	67	61	57		75	66	61	57		65	60	57		65	60	57		64	59	56
10	73	64	58	54		72	63	58	54		62	57	54		62	57	54		61	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145953
5°	140017
10°	122665
15°	98593
20°	75747
25°	57318
30°	41424
35°	27519
40°	16688
45°	9706
50°	6209
55°	5046
60°	4386
65°	3891
70°	3206
75°	3219
80°	2399
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9706 cd/sqm

TEST NUMBER: P1282976

CATALOG NUMBER: P3AS09R25B2750DE010 E3DLP1WMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.9	14.4
10°-20°	120.1	29.9
20°-30°	108.6	27.0
30°-40°	65.2	16.2
40°-50°	25.9	6.4
50°-60°	12.0	3.0
60°-70°	7.3	1.8
70°-80°	3.9	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	286.6	71.3
0°-40°	351.9	87.5
0°-60°	389.7	96.9
0°-90°	402.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	402.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	666	
5°	636	58
15°	434	120
25°	237	109
35°	103	65
45°	31	26
55°	13	12
65°	8	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1282976

CATALOG NUMBER: P3AS09R25B2750DE010 E3DLP1WMH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	665.6
1°	665.6
2°	662.4
3°	655.5
4°	646.8
5°	636.1
6°	622.3
7°	606.7
8°	588.5
9°	570.3
10°	550.9
11°	528.3
12°	505.1
13°	481.9
14°	458.8
15°	434.3
17.5°	376.7
20°	324.6
22.5°	277.6
25°	236.9
27.5°	198.7
30°	163.6
32.5°	131.6
35°	102.8
37.5°	78.3
40°	58.3
42.5°	42.6
45°	31.3
47.5°	23.8
50°	18.2
52.5°	15.0
55°	13.2
57.5°	11.3
60°	10.0
62.5°	8.1
65°	7.5
67.5°	6.3
70°	5.0
72.5°	4.4
75°	3.8
77.5°	3.1
80°	1.9
82.5°	1.3
85°	1.3
87.5°	0.6



TEST NUMBER: P1282976

CATALOG NUMBER: P3AS09R25B2750DE010 E3DLP1WMH_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)