

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283760

Luminaire Tested: P3AS09R55B2750DE010 E3D1WMH_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283760
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R55B2750DE010 E3D1WMH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 4000K CCT AND, 80CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 757.0 lumens
Efficiency: N/A
Efficacy: 57.8 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283760

CATALOG NUMBER: P3AS09R55B2750DE010 E3D1WMH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1283760

CATALOG NUMBER: P3AS09R55B2750DE010 E3D1WMH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	102	102	102	102	102	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	96	96	96	96	96	96	96	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	91	91	91	91	91	91	91	91	91	91	91	89
3	104	98	94	90	102	97	93	90	95	91	88	92	89	87	90	88	86	86	86	86	86	86	86	86	86	86	86	86	84
4	100	93	88	84	98	92	87	84	90	86	83	88	84	82	86	83	81	81	81	81	81	81	81	81	81	81	81	81	79
5	95	88	82	79	94	87	82	78	85	81	78	84	80	77	82	79	76	76	76	76	76	76	76	76	76	76	76	76	75
6	91	83	78	74	90	82	77	74	81	76	73	80	76	73	78	75	72	72	72	72	72	72	72	72	72	72	72	72	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	68	68	68	68	68	68	68	68	68	68	68	67
8	83	75	69	66	82	74	69	65	73	69	65	72	68	65	71	68	65	65	65	65	65	65	65	65	65	65	65	65	63
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	61	61	61	61	61	61	61	61	61	61	61	60
10	77	68	62	59	76	67	62	59	67	62	59	66	62	59	65	61	58	58	58	58	58	58	58	58	58	58	58	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	219522
5°	211754
10°	219323
15°	216233
20°	200124
25°	161840
30°	97002
35°	32873
40°	9046
45°	4000
50°	1194
55°	229
60°	132
65°	156
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4000 cd/sqm

TEST NUMBER: P1283760

CATALOG NUMBER: P3AS09R55B2750DE010 E3D1WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.1	12.3
10°-20°	265.2	35.0
20°-30°	294.8	38.9
30°-40°	91.8	12.1
40°-50°	11.0	1.5
50°-60°	0.9	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	653.0	86.3
0°-40°	744.8	98.4
0°-60°	756.7	100.0
0°-90°	757.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	757.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1001	
5°	962	93
15°	952	265
25°	669	295
35°	123	92
45°	13	11
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1283760

CATALOG NUMBER: P3AS09R55B2750DE010 E3D1WMH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1001.1
1°	997.4
2°	987.6
3°	975.5
4°	964.6
5°	962.0
6°	964.9
7°	970.9
8°	977.8
9°	983.3
10°	985.0
11°	983.8
12°	979.2
13°	972.1
14°	963.7
15°	952.5
16°	939.6
17°	923.2
18°	904.8
19°	882.6
20°	857.6
21°	829.1
22°	795.5
23°	758.4
24°	715.8
25°	668.9
26°	617.5
27°	562.8
28°	504.4
29°	444.3
30°	383.1
31°	321.5
32°	261.4
32.5°	234.7
33°	207.1
34°	160.2
35°	122.8
36°	93.5
37°	69.3
37.5°	59.2
38°	51.5
39°	39.1
40°	31.6
42.5°	20.1
45°	12.9

TEST NUMBER: P1283760

CATALOG NUMBER: P3AS09R55B2750DE010 E3D1WMH_4000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	7.8
50°	3.5
52.5°	1.2
55°	0.6
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)