

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283792

Luminaire Tested: P3AS09R55B2750DE010 E3DLD1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283792
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R55B2750DE010 E3DLD1GPH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 2700K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 243.0 lumens
Efficiency: N/A
Efficacy: 18.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283792

CATALOG NUMBER: P3AS09R55B2750DE010 E3DLD1GPH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1283792

CATALOG NUMBER: P3AS09R55B2750DE010 E3DLD1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93		91
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89	86	84		82
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82	79	76		74
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76	73	69		68
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71	67	64		62
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66	62	58		57
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62	57	54		52
8	73	62	55	51	72	62	55	51	60	55	50		59	54	50		58	53	50		48
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55	50	46		45
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		52	47	43		42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	45698
5°	45102
10°	43330
15°	40522
20°	36963
25°	32978
30°	28840
35°	23958
40°	18893
45°	12808
50°	7846
55°	4052
60°	3772
65°	3580
70°	3334
75°	2881
80°	2904
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 12808 cd/sqm

TEST NUMBER: P1283792

CATALOG NUMBER: P3AS09R55B2750DE010 E3DLD1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.2	7.9
10°-20°	49.9	20.5
20°-30°	62.5	25.7
30°-40°	55.8	23.0
40°-50°	32.7	13.4
50°-60°	11.3	4.6
60°-70°	6.8	2.8
70°-80°	3.8	1.6
80°-90°	1.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	131.6	54.2
0°-40°	187.3	77.1
0°-60°	231.3	95.2
0°-90°	243.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	243.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	208	
5°	205	19
15°	178	50
25°	136	62
35°	90	56
45°	41	33
55°	11	11
65°	7	7
75°	3	4
85°	1	1
90°	0	

TEST NUMBER: P1283792

CATALOG NUMBER: P3AS09R55B2750DE010 E3DLD1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	208.4
2.5°	207.2
5°	204.9
7.5°	200.3
10°	194.6
12.5°	187.4
15°	178.5
17.5°	169.0
20°	158.4
22.5°	147.5
25°	136.3
27.5°	125.1
30°	113.9
32.5°	101.9
35°	89.5
37.5°	77.5
40°	66.0
42.5°	53.7
45°	41.3
47.5°	31.6
50°	23.0
52.5°	14.9
55°	10.6
57.5°	9.5
60°	8.6
62.5°	7.7
65°	6.9
67.5°	6.0
70°	5.2
72.5°	4.3
75°	3.4
77.5°	2.9
80°	2.3
82.5°	1.4
85°	0.9
87.5°	0.6
90°	0.0

(END OF REPORT)