

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282985

Luminaire Tested: P3AS09R25B2750DE010 E3PHLD1MW_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282985
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R25B2750DE010 E3PHLD1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 80CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 471.0 lumens
Efficiency: N/A
Efficacy: 36.0 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.71
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282985

CATALOG NUMBER: P3AS09R25B2750DE010 E3PHLD1MW_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1282985

CATALOG NUMBER: P3AS09R25B2750DE010 E3PHLD1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		95
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87
3	97	89	83	78	95	88	82	77	85	80	76		83	78	75		80
4	91	82	75	70	89	81	74	69	78	73	69		76	72	68		74
5	86	76	68	63	84	75	68	63	73	67	62		71	66	62		69
6	81	70	63	58	79	69	62	57	68	62	57		66	61	57		65
7	76	65	58	53	75	64	58	53	63	57	53		62	56	52		61
8	72	61	54	49	71	60	54	49	59	53	49		58	53	49		57
9	68	57	50	46	67	57	50	46	56	50	46		55	49	45		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	43		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	122885
5°	116663
10°	101045
15°	82248
20°	64989
25°	51826
30°	42006
35°	34211
40°	28367
45°	23878
50°	20230
55°	17815
60°	15613
65°	13594
70°	11925
75°	10082
80°	7450
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23878 cd/sqm

TEST NUMBER: P1282985

CATALOG NUMBER: P3AS09R25B2750DE010 E3PHLD1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	10.2
10°-20°	100.5	21.3
20°-30°	99.0	21.0
30°-40°	80.6	17.1
40°-50°	59.8	12.7
50°-60°	41.8	8.9
60°-70°	26.1	5.6
70°-80°	12.6	2.7
80°-90°	2.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	247.6	52.6
0°-40°	328.2	69.7
0°-60°	429.8	91.3
0°-90°	471.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	471.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	560	
5°	530	48
15°	362	100
25°	214	99
35°	128	81
45°	77	60
55°	47	42
65°	26	26
75°	12	13
85°	2	2
90°	0	

TEST NUMBER: P1282985

CATALOG NUMBER: P3AS09R25B2750DE010 E3PHLD1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	560.4
2.5°	552.8
5°	530.0
7.5°	495.3
10°	453.8
12.5°	408.1
15°	362.3
17.5°	317.5
20°	278.5
22.5°	244.7
25°	214.2
27.5°	187.9
30°	165.9
32.5°	145.6
35°	127.8
37.5°	112.6
40°	99.1
42.5°	87.2
45°	77.0
47.5°	67.7
50°	59.3
52.5°	52.5
55°	46.6
57.5°	40.6
60°	35.6
62.5°	30.5
65°	26.2
67.5°	22.0
70°	18.6
72.5°	15.2
75°	11.9
77.5°	8.5
80°	5.9
82.5°	3.4
85°	1.7
87.5°	0.8
90°	0.0

(END OF REPORT)