

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283897

Luminaire Tested: P3AS09R60B2750DE010 E3D1WH_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283897
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R60B2750DE010 E3D1WH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R60 optic, 2700K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 701.0 lumens
Efficiency: N/A
Efficacy: 53.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283897

CATALOG NUMBER: P3AS09R60B2750DE010 E3D1WH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1283897

CATALOG NUMBER: P3AS09R60B2750DE010 E3D1WH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94						
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88						
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82						
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77						
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72						
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	71	69	67						
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63						
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59						
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56						
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	183669
5°	173387
10°	168890
15°	165018
20°	153430
25°	137161
30°	104776
35°	60498
40°	23473
45°	9768
50°	2149
55°	344
60°	263
65°	156
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9768 cd/sqm

TEST NUMBER: P1283897

CATALOG NUMBER: P3AS09R60B2750DE010 E3D1WH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.4	10.6
10°-20°	202.5	28.9
20°-30°	253.6	36.2
30°-40°	141.8	20.2
40°-50°	26.9	3.8
50°-60°	1.4	0.2
60°-70°	0.3	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	530.5	75.7
0°-40°	672.2	95.9
0°-60°	700.6	99.9
0°-90°	701.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	701.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	838	
5°	788	74
15°	727	202
25°	567	254
35°	226	142
45°	32	27
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1283897

CATALOG NUMBER: P3AS09R60B2750DE010 E3D1WH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	837.6
1°	834.2
2°	823.3
3°	810.4
4°	798.3
5°	787.7
6°	779.7
7°	772.8
8°	767.6
9°	762.8
10°	758.5
11°	754.2
12°	749.3
13°	743.3
14°	736.1
15°	726.9
16°	715.7
17°	703.1
18°	688.8
19°	672.4
20°	657.5
21°	641.5
22°	624.8
23°	607.3
24°	588.1
25°	566.9
26°	542.0
27°	514.2
28°	482.9
29°	449.6
30°	413.8
31°	377.7
32°	340.4
32.5°	320.0
33°	301.7
34°	263.5
35°	226.0
36°	192.1
37°	156.3
37.5°	139.9
38°	123.9
39°	99.8
40°	82.0
42.5°	49.9
45°	31.5



TEST NUMBER: P1283897

CATALOG NUMBER: P3AS09R60B2750DE010 E3D1WH_2700K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	17.5
50°	6.3
52.5°	1.4
55°	0.9
57.5°	0.6
60°	0.6
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)