

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283047

Luminaire Tested: P3AS09R30B2750DE010 E3DL1GPH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1283047  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R30B2750DE010 E3DL1GPH\_2700K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 2700K CCT AND, 90CRI , E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 304.0 lumens  
Efficiency: N/A  
Efficacy: 23.2 lumens/watt  
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 13.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1283047  
CATALOG NUMBER: P3AS09R30B2750DE010 E3DL1GPH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1283047

CATALOG NUMBER: P3AS09R30B2750DE010 E3DL1GPH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	75	75	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	78	75	73	71	71	71	71
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	69	69	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63	63	63	63

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	177398
5°	168853
10°	142015
15°	102430
20°	63519
25°	36123
30°	20079
35°	10922
40°	5754
45°	3132
50°	1672
55°	1109
60°	1009
65°	1038
70°	898
75°	763
80°	758
85°	755

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3132 cd/sqm



TEST NUMBER: P1283047

CATALOG NUMBER: P3AS09R30B2750DE010 E3DL1GPH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	69.1	22.7
10°-20°	122.8	40.4
20°-30°	71.0	23.3
30°-40°	26.9	8.9
40°-50°	8.3	2.7
50°-60°	2.8	0.9
60°-70°	1.9	0.6
70°-80°	1.0	0.3
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	262.8	86.4
0°-40°	289.7	95.3
0°-60°	300.8	98.9
0°-90°	304.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	304.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	809	
5°	767	69
15°	451	123
25°	149	71
35°	41	27
45°	10	8
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1283047

CATALOG NUMBER: P3AS09R30B2750DE010 E3DL1GPH\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	809.0
1°	808.4
2°	803.5
3°	794.3
4°	782.8
5°	767.1
6°	746.9
7°	724.5
8°	699.6
9°	669.7
10°	637.8
11°	603.4
12°	566.9
13°	528.7
14°	489.9
15°	451.2
17.5°	355.8
20°	272.2
22.5°	201.9
25°	149.3
27.5°	108.6
30°	79.3
32.5°	57.1
35°	40.8
37.5°	28.4
40°	20.1
42.5°	14.1
45°	10.1
47.5°	6.9
50°	4.9
52.5°	3.4
55°	2.9
57.5°	2.6
60°	2.3
62.5°	2.0
65°	2.0
67.5°	1.7
70°	1.4
72.5°	1.1
75°	0.9
77.5°	0.9
80°	0.6
82.5°	0.6
85°	0.3
87.5°	0.0



TEST NUMBER: P1283047  
CATALOG NUMBER: P3AS09R30B2750DE010 E3DL1GPH\_2700K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)