

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283065

Luminaire Tested: P3AS09R30B2750DE010 E3DL1MW_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283065
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R30B2750DE010 E3DL1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 4000K CCT AND, 80CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 621.0 lumens
Efficiency: N/A
Efficacy: 47.4 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283065
CATALOG NUMBER: P3AS09R30B2750DE010 E3DL1MW_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1283065

CATALOG NUMBER: P3AS09R30B2750DE010 E3DL1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	97	97	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	92	92	92	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	87	87	87	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	83	83	83	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	79	79	79	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	76	76	76	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	79	75	73	73	73	73	71
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	70	70	70	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	67	67	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	65	65	65	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	362383
5°	344903
10°	290108
15°	209218
20°	129768
25°	73819
30°	40994
35°	22299
40°	11765
45°	6357
50°	3411
55°	2256
60°	2061
65°	2127
70°	1859
75°	1525
80°	1515
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6357 cd/sqm



TEST NUMBER: P1283065

CATALOG NUMBER: P3AS09R30B2750DE010 E3DL1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.1	22.7
10°-20°	250.8	40.4
20°-30°	144.9	23.3
30°-40°	55.0	8.9
40°-50°	16.9	2.7
50°-60°	5.7	0.9
60°-70°	3.8	0.6
70°-80°	2.1	0.3
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	536.8	86.4
0°-40°	591.8	95.3
0°-60°	614.4	98.9
0°-90°	621.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	621.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1653	
5°	1567	141
15°	922	251
25°	305	145
35°	83	55
45°	20	17
55°	6	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1283065
CATALOG NUMBER: P3AS09R30B2750DE010 E3DL1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1652.6
1°	1651.4
2°	1641.4
3°	1622.6
4°	1599.2
5°	1566.9
6°	1525.8
7°	1480.1
8°	1429.0
9°	1368.0
10°	1302.9
11°	1232.5
12°	1158.0
13°	1080.0
14°	1000.8
15°	921.6
17.5°	726.8
20°	556.1
22.5°	412.4
25°	305.1
27.5°	221.7
30°	161.9
32.5°	116.7
35°	83.3
37.5°	58.1
40°	41.1
42.5°	28.7
45°	20.5
47.5°	14.1
50°	10.0
52.5°	7.0
55°	5.9
57.5°	5.3
60°	4.7
62.5°	4.1
65°	4.1
67.5°	3.5
70°	2.9
72.5°	2.3
75°	1.8
77.5°	1.8
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.0



TEST NUMBER: P1283065
CATALOG NUMBER: P3AS09R30B2750DE010 E3DL1MW_4000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)