

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283963

Luminaire Tested: P3AS09R60B2750DE010 E3DLD1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283963
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R60B2750DE010 E3DLD1WMH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 475.0 lumens
Efficiency: N/A
Efficacy: 36.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283963

CATALOG NUMBER: P3AS09R60B2750DE010 E3DLD1WMH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1283963

CATALOG NUMBER: P3AS09R60B2750DE010 E3DLD1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0				0				0
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91											
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82											
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74											
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67											
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61											
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56											
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51											
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47											
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44											
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	84313
5°	83381
10°	80493
15°	76028
20°	70099
25°	63463
30°	56338
35°	48158
40°	38272
45°	27011
50°	16136
55°	8143
60°	7850
65°	7160
70°	6668
75°	6354
80°	5809
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 27011 cd/sqm

TEST NUMBER: P1283963

CATALOG NUMBER: P3AS09R60B2750DE010 E3DLD1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.6	7.5
10°-20°	93.6	19.7
20°-30°	120.2	25.3
30°-40°	111.4	23.5
40°-50°	67.9	14.3
50°-60°	22.6	4.8
60°-70°	13.8	2.9
70°-80°	7.8	1.6
80°-90°	2.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	249.4	52.5
0°-40°	360.8	76.0
0°-60°	451.3	95.0
0°-90°	475.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	475.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	384	
5°	379	36
15°	335	94
25°	262	120
35°	180	111
45°	87	68
55°	21	23
65°	14	14
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1283963

CATALOG NUMBER: P3AS09R60B2750DE010 E3DLD1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	384.5
2.5°	382.8
5°	378.8
7.5°	371.3
10°	361.5
12.5°	349.4
15°	334.9
17.5°	318.2
20°	300.4
22.5°	281.3
25°	262.3
27.5°	242.7
30°	222.5
32.5°	202.4
35°	179.9
37.5°	156.2
40°	133.7
42.5°	110.1
45°	87.1
47.5°	67.5
50°	47.3
52.5°	28.2
55°	21.3
57.5°	19.6
60°	17.9
62.5°	15.6
65°	13.8
67.5°	12.1
70°	10.4
72.5°	8.6
75°	7.5
77.5°	5.8
80°	4.6
82.5°	2.9
85°	1.7
87.5°	1.2
90°	0.0

(END OF REPORT)