

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283965

Luminaire Tested: P3AS09R60B2750DE010 E3DLD1WMH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283965
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R60B2750DE010 E3DLD1WMH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R60 optic, 4000K CCT AND, 80CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 484.0 lumens
Efficiency: N/A
Efficacy: 36.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283965

CATALOG NUMBER: P3AS09R60B2750DE010 E3DLD1WMH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1283965

CATALOG NUMBER: P3AS09R60B2750DE010 E3DLD1WMH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	85914
5°	84944
10°	82007
15°	77481
20°	71406
25°	64673
30°	57401
35°	49068
40°	39016
45°	27507
50°	16443
55°	8296
60°	7982
65°	7316
70°	6796
75°	6439
80°	5935
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 27507 cd/sqm

TEST NUMBER: P1283965

CATALOG NUMBER: P3AS09R60B2750DE010 E3DLD1WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.3	7.5
10°-20°	95.4	19.7
20°-30°	122.5	25.3
30°-40°	113.6	23.5
40°-50°	69.1	14.3
50°-60°	23.0	4.8
60°-70°	14.0	2.9
70°-80°	7.9	1.6
80°-90°	2.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	254.1	52.5
0°-40°	367.7	76.0
0°-60°	459.9	95.0
0°-90°	484.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	484.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	392	
5°	386	36
15°	341	95
25°	267	122
35°	183	114
45°	89	69
55°	22	23
65°	14	14
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1283965

CATALOG NUMBER: P3AS09R60B2750DE010 E3DLD1WMH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	391.8
2.5°	390.1
5°	385.9
7.5°	378.3
10°	368.3
12.5°	356.0
15°	341.3
17.5°	324.3
20°	306.0
22.5°	286.7
25°	267.3
27.5°	247.3
30°	226.7
32.5°	206.2
35°	183.3
37.5°	159.2
40°	136.3
42.5°	112.2
45°	88.7
47.5°	68.7
50°	48.2
52.5°	28.8
55°	21.7
57.5°	20.0
60°	18.2
62.5°	15.9
65°	14.1
67.5°	12.3
70°	10.6
72.5°	8.8
75°	7.6
77.5°	5.9
80°	4.7
82.5°	2.9
85°	1.8
87.5°	1.2
90°	0.0

(END OF REPORT)