

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283984

Luminaire Tested: P3AS09R60B2750DE010 E3DLP1MW_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283984
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R60B2750DE010 E3DLP1MW_3500K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R60 optic, 3500K CCT AND, 80CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 430.0 lumens
Efficiency: N/A
Efficacy: 32.8 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283984

CATALOG NUMBER: P3AS09R60B2750DE010 E3DLP1MW_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1283984

CATALOG NUMBER: P3AS09R60B2750DE010 E3DLP1MW_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	108982
5°	106537
10°	99731
15°	89467
20°	76937
25°	63633
30°	50286
35°	37343
40°	25705
45°	16126
50°	8870
55°	5199
60°	4649
65°	3995
70°	3398
75°	3474
80°	3031
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16126 cd/sqm

TEST NUMBER: P1283984

CATALOG NUMBER: P3AS09R60B2750DE010 E3DLP1MW_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.1	10.5
10°-20°	109.5	25.5
20°-30°	120.1	27.9
30°-40°	87.5	20.3
40°-50°	41.3	9.6
50°-60°	13.5	3.1
60°-70°	7.7	1.8
70°-80°	4.1	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	274.6	63.9
0°-40°	362.1	84.2
0°-60°	416.9	97.0
0°-90°	430.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	430.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	497	
5°	484	45
15°	394	109
25°	263	120
35°	140	87
45°	52	41
55°	14	14
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1283984

CATALOG NUMBER: P3AS09R60B2750DE010 E3DLP1MW_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	497.0
2.5°	494.0
5°	484.0
7.5°	468.6
10°	447.9
12.5°	423.1
15°	394.1
17.5°	362.8
20°	329.7
22.5°	296.1
25°	263.0
27.5°	229.9
30°	198.6
32.5°	168.4
35°	139.5
37.5°	113.5
40°	89.8
42.5°	69.1
45°	52.0
47.5°	37.8
50°	26.0
52.5°	17.1
55°	13.6
57.5°	11.8
60°	10.6
62.5°	8.9
65°	7.7
67.5°	6.5
70°	5.3
72.5°	4.7
75°	4.1
77.5°	3.0
80°	2.4
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)